Product datasheet

Specifications





GLANDPLATE 2 ENTRIES DIAMETER 33 TO 72MM DIRECT MOUNTING PRISMA G IP55

08899

! Discontinued on: 17 Jan 2022

! End-of-service on: 17 Dec 2022

① Discontinued

Price: 793.37 ZAR

Main

| Range Of Product | Prisma G |
|---------------------------------------|---------------------------|
| Range | Prisma |
| Range Compatibility | Prisma Prisma G enclosure |
| Product Or Component Type | Gland plate |
| Accessory / Separate Part Category | Enclosure accessory |
| Product Compatibility | IP55 enclosure |

Complementary

| Enclosure/Cubicle Description | Wall-mounted enclosure - width 600 mm |
|-------------------------------|---------------------------------------|
| Type Of Gland Plate | Knockouts |
| Mounting Location | Top Bottom |
| Material | Insulated material |
| Cable Entry Number | 2 diameter: 3372 mm |
| Quantity Per Set | Set of 1 |
| Depth | 180 mm |
| Net Weight | 0.44 kg |
| Colour | White (RAL 9001) |

Environment

Ip Degree Of Protection IP55

Packing Units

| Unit Type Of Package 1 | PCE |
|------------------------------|---------|
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 4 cm |
| Package 1 Width | 16 cm |
| Package 1 Length | 24.5 cm |
| Package 1 Weight | 420 g |

Excluding VAT and subject to change. Please check with your local distributor through "Where to buy"



Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

| ⊘ | Reach Free Of Svhc |
|----------|------------------------------------|
| ⊘ | Toxic Heavy Metal Free |
| ⊘ | Mercury Free |
| ⊘ | Rohs Exemption Information Yes |
| Ø | Halogen Free Plastic Parts Product |

Certifications & Standards

| Eu Rohs Directive | Pro-active compliance (Product out of EU RoHS legal scope) |
|--------------------------|---|
| | EU RoHS Declaration |
| China Rohs Regulation | China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope) |
| Environmental Disclosure | Product Environmental Profile |