

# Product datasheet

Specifications



## mini Kaedra - for modular device - 1 openings - 3 modules

13956

⚠ Discontinued on: 02 Jan 2024

Price: 202.02 ZAR

⚠ Discontinued

### Main

Range	Kaedra
Product Or Component Type	Weatherproof enclosure
Enclosure Type	Mini enclosure for modular device
Accessories Included With Enclosure	1 marking kit
Mounting Plate Description	Without mounting plate

### Complementary

Enclosure Mounting	Surface
9 Mm Pitches	6
Number Of 18 Mm Modules Per Row	3
Total Number Of 18 Mm Modules	3
Number Of Horizontal Rows	1
Electrical Insulation Class	Class II Double insulation
Provided Equipment	1 marking kit
Type Of Front Cover	Transparent
[In] Rated Current	32 A
Type Of Rail	DIN
Number Of Pre-Cutouts Pg Iso	1
Locking Options Description	Optional keylock
Enclosure Material	Self-extinguishing polymer
Width	80 mm
Height	150 mm
Depth	98 mm
Internal Depth	56 mm
Colour	Door: transparent green Enclosure: light grey (RAL 7035)

### Environment

Excluding VAT and subject to change. Please check with your local distributor through "Where to buy"

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Standards	IEC 60529 IEC 60439-3 EN 50102 EN 50262 IEC 670
Fire Resistance	750 °C conforming to IEC 60695-2-1
Ip Degree Of Protection	IP65 conforming to IEC 60529
Ik Degree Of Protection	IK09 conforming to EN 50102
Environmental Characteristics (Uv)	UV resistant: class 3 conforming to ISO 4582:2010 Ultraviolet degradation test conforming to ISO 4892-2:2013
Overvoltage Category	II
Ambient Air Temperature For Operation	-25...60 °C

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	8.0 cm
Package 1 Width	9.8 cm
Package 1 Length	15.0 cm
Package 1 Weight	270.0 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	20
Package 2 Height	21.7 cm
Package 2 Width	34 cm
Package 2 Length	40 cm
Package 2 Weight	5.75 kg
Unit Type Of Package 3	P12
Number Of Units In Package 3	480
Package 3 Height	101 cm
Package 3 Width	80 cm
Package 3 Length	120 cm
Package 3 Weight	136.56 kg

## Contractual warranty

Warranty	18 months
----------	-----------

# Sustainability

**Green Premium™ label** is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)

## Well-being performance

 Mercury Free	
 Rohs Exemption Information	<a href="#">Yes</a>
Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information