

Product datasheet

Specifications



rectangular sensor for earth leakage protection. MasterPact NW. ComPact NS1600b to NS3200. 3200A. inside dimensions 470mm x 160mm

33574

Price: 40,284.86 ZAR

Main

| | |
|---------------------|------------------------------------------------------------|
| Device Short Name | sensor + Vigi cable |
| Device Application | Power supply |
| Range Compatibility | Masterpact MasterPact NW ComPact ComPact NS1600b...3200 |

Complementary

| | |
|------------------------------------|-----------------------------------------------------------------------|
| Current Transformer Type | Earth leakage protection |
| [In] Rated Current | 800 A 1000 A 1250 A 1600 A 2000 A 2500 A 3200 A |
| Height | Inside: 160 mm Outside: 281 mm |
| Width | Inside: 470 mm Outside: 572 mm |
| Depth | 72 mm |
| Accessory / Separate Part Category | Spare part for ComPact NS1600b...3200 Spare part for MasterPact NW |

Packing Units

| | |
|------------------------------|------------|
| Unit Type Of Package 1 | PCE |
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 18.000 cm |
| Package 1 Width | 65.000 cm |
| Package 1 Length | 34.000 cm |
| Package 1 Weight | 18.450 kg |
| Unit Type Of Package 2 | P12 |
| Number Of Units In Package 2 | 9 |
| Package 2 Height | 67.000 cm |
| Package 2 Width | 80.000 cm |
| Package 2 Length | 120.000 cm |
| Package 2 Weight | 180.675 kg |

Excluding VAT and subject to change. Please check with your local distributor through "Where to buy"

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Well-being performance

| | | |
|-----------------------|----------------------------|-------------------------------------------------------------------------------------------------------------|
| ✓ | Reach Free Of Svhc | |
| ✓ | Toxic Heavy Metal Free | |
| ✓ | Mercury Free | |
| ✓ | Rohs Exemption Information | Yes |
| | | |
| Reach Regulation | | REACH Declaration |
| | | |
| Eu Rohs Directive | | Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration |
| | | |
| China Rohs Regulation | | China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope) |