





APC 19" Rack LCD Console

AP5719

Price: 38,542.01 ZAR

Overview

Presentation	1U rack-mountable keyboard, mouse, and LCD console with US English keyboard layout.
Lead Time	Usually in Stock

Main		
Main Input Voltage	100 V	
	240 V	
Number Of Rack Unit	1U	
Provided Equipment	C13-C14 power cord	
	Documentation CD	
	Firmware upgrade cable	
	Installation guide	
	NEMA 5-15 power cord	
	PS2 KVM cable	
	Rack mounting hardware	
	Single user rack mount kit	
	USB cable	
	USB KVM cable	

Physical

Colour	Black
Height	4.4 cm
Width	48.2 cm
Depth	66.5 cm
Net Weight	17.4 kg
Mounting Location	Front Rear
Mounting Preference	No preference
Mounting Mode	Rack-mounted
Maximum Mounting Depth	104.98 cm
Minimum Mounting Depth	68 cm

Input

Network Frequency 50/60 Hz

Conformance

Excluding VAT and subject to change. Please check with your local distributor through "Where to buy"

Product Certifications	C-Tick
	CE
	Industry Canada
	KCC
	NOM
	UL listed
	VCCI class A
	VDE
	TAA compliance
Standards	EN 55022 class A
	EN 55024
	EN 60950
	FCC part 15 class A
	IEC 60950

Environmental

Ambient Air Temperature For Operation

0...40 °C

Supported Hardware

Display Size	19 inch
Trackball Type	PS/2 touchpad USB mouse
Display Type	LCD display
Display Power Consumption	19 W
Pixel Size	0.26

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	15.2 cm
Package 1 Width	82.6 cm
Package 1 Length	67.3 cm
Package 1 Weight	20.99 kg

Contractual warranty

Warranty 2 years repair or replace



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >







Take-back Transparency RoHS/REACh

Resource performance



Take-Back Program Available

Well-being performance

Reach Free Of Svhc

Mercury Free

Lead Free

Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation

Eu Rohs Directive

Compliant with Exemptions

Environmental Disclosure

Product Environmental Profile

The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins