





APC NetShelter SX, Server Rack Enclosure, 48U, Shock Packaging, 2000 lbs, Black, 2258H x 600W x 1070D mm

AR3107SP

Overview

Presentation	NetShelter SX cabinet and packaging system designed to safely integrate, transport, unload and deploy up to 2000 lbs (907 kg) of IT equipment. The cabinet is paired with a shock absorbing pallet, unloading ramp, and impact resistant shell. The system has been engineered, tested and approved for secure shipment of fully converged systems such as being certified with Cisco® for pre-racking and shipping Cisco Unified Computing System (UCS).
L ead Time	Liqually Shins within 6 Weeks

Main

Product Or Component Type	Rack enclosure
Number Of Rack Unit	48U
Provided Equipment	Baying hardware Documentation CD Key(s) Keyed-alike doors and side panels Leveling feet Mounting hardware Pre-installed casters Side panels

Physical

Height	225.8 cm
Width	60 cm
Depth	107 cm
Net Weight	138.23 kg
Colour	Black
Mounting Preference	No preference
Mounting Mode	Not rack-mountable
Maximum Mounting Depth	91.49 cm
Minimum Mounting Depth	19.1 cm
Rack Width	19"
Marking	14 gauge EIA mounting rail 16 gauge front door 16 gauge post 18 gauge rear door 18 gauge roof 18 gauge side panels
Permanent Permissible Load	1020.58 kg dynamic 1700.97 kg static

Conformance

Excluding VAT and subject to change. Please check with your local distributor through "Where to buy"

Standards

UL 2416

UL 60950-1

EIA-310E

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	245.1 cm
Package 1 Width	132.1 cm
Package 1 Length	110.5 cm
Package 1 Weight	240.86 kg

Contractual warranty

Warranty 5 year repair or replace



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >







Yes

Take-back Transparency RoHS/REACh

Resource performance



Take-Back Program Available

Well-being performance

Reach Free Of Svhc

Toxic Heavy Metal Free

Mercury Free

Rohs Exemption Information

Certifications & Standards

Reach Regulation

Eu Rohs Directive

Pro-active compliance (Product out of EU RoHS legal scope)

EU RoHS Declaration

Environmental Disclosure

Product Environmental Profile