Product datasheet

Specifications



NetShelter SX colocation 2x20U 600mm wide x 1070mm deep enclosure- sides black

AR3200

Price: 45,512.37 ZAR

Overview		
Presentation	Two compartment enclosure for colocation facilities with customers requiring a minimal amount of rack space. This multi-tenant, security enhanced enclosure is provided with a compact width to optimize data center space.	
Lead Time	Usually in Stock	
Main		
Product Or Component Type	Rack enclosure	
Number Of Rack Unit	42U	
Provided Equipment	3-digit combination style handles Adjustable vertical mounting rails Baying hardware Documentation CD Door key Installation guide Leveling feet Pre-installed casters	

Rack mounting hardware

Roof

Physical

Height	199.1 cm
Width	60 cm
Depth	107 cm
Net Weight	140.7 kg
Colour	Black
Mounting Preference	No preference
Mounting Mode	Not rack-mountable
Maximum Mounting Depth	94.49 cm
Rack Width	19"
Marking	14 gauge EIA mounting rail 16 gauge front door 16 gauge post 18 gauge rear door 18 gauge roof 18 gauge side panels
Permanent Permissible Load	1020.58 kg dynamic 1700.97 kg static

Conformance

Excluding VAT and subject to change. Please check with your local distributor through "Where to buy"

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	211.7 cm
Package 1 Width	74.6 cm
Package 1 Length	115.6 cm
Package 1 Weight	168.35 kg

Contractual warranty

Warranty

5 year repair or replace

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Take-back Transparency RoHS/REACh

Resource performance

Take-Back Program Available

Well-being performance

Reach Free Of Svhc

Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile