# **Product datasheet**

Specifications





Feed unit, Canalis KSA, 630A, right mounting, without line protection, polarity 3L+N+PE, white RAL9001

KSA630ABD4

Price: 27,509.28 ZAR

#### Main

Range Of Product	Canalis	
Product Name	KS	
Device Short Name	KSA	
Product Compatibility	Canalis KSA busbar trunking 5001000 A	
Offer Type	Classic Rising main	
Product Or Component Type	Feed unit	
Conductors Material	Aluminium	
[le] Rated Operational Current	630 A	
[Ue] Rated Operational Voltage	230690 V	
Number Of Circuits	1	
Busbar Trunking Polarity	3L + N + PE	
Protection Type	Without protection	
Control Type	Without	
Colour	White (RAL 9001)	

### Complementary

Provided Equipment	End cover
Mounting Location	Right
Mounting Mode	By screws
Mounting Support	Busbar
Body Material	Metal
Connections - Terminals	Lug for 300 mm² rigid Lug for 300 mm² flexible
Width	753 mm
Depth	288 mm
Height	457 mm
Net Weight	22 kg
Standards	IEC 61439-1 IEC 61439-6

#### **Environment**

Excluding VAT and subject to change. Please check with your local distributor through "Where to buy"

Ip Degree Of Protection	IP55 conforming to IEC 60529
Ik Degree Of Protection	IK08 conforming to IEC 62262

# **Packing Units**

•	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	29.4 cm
Package 1 Width	50.0 cm
Package 1 Length	76.1 cm
Package 1 Weight	24.0 kg
Unit Type Of Package 2	P06
Number Of Units In Package 2	2
Package 2 Height	80.0 cm
Package 2 Width	80.0 cm
Package 2 Length	60.0 cm
Package 2 Weight	60.0 kg

# **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

#### Well-being performance

<b>⊘</b>	Reach Free Of Svhc
<b>⊘</b>	Toxic Heavy Metal Free
<b>⊘</b>	Mercury Free
<b>⊘</b>	Rohs Exemption Information Yes
<b>⊘</b>	Halogen Free Product

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration  Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations

## **Product datasheet**

### KSA630ABD4

### **Dimensions Drawings**

#### **Dimensions**



