Product datasheet

Specifications





TeSys LE - enclosed DOL starter - 1.8...2.6 A - 220 V AC coil

LE1M35M708

Price: 1,167.68 ZAR

Main

Range	TeSys	
Product Name	TeSys LE	
Device Short Name	LE1M	
Product Or Component Type	Enclosed DOL starter	
Device Application	Standard	
Utilisation Category	у АС-3	
Device Composition	Contactor Earth terminal Neutral terminal Thermal overload relay	
Thermal Protection Adjustment Range	1.82.6 A	
Motor Power Kw	0.37 kW at 240 V AC 50/60 Hz 0.75 kW at 415 V AC 50/60 Hz 0.37 kW at 220/230 V AC 50/60 Hz 1.1 kW at 380/400 V AC 50/60 Hz	
[Uc] Control Circuit Voltage	220 V AC 50/60 Hz	
Control Type	Push-button start green I Push-button stop/reset red O	

Complementary

Local Signalling	Operating: LED (yellow)	
Cable Entry Number	2 ISO20 top	
	2 ISO25 top	
	2 Pg 13 top	
	2 Pg 21 top	
	2 ISO20 bottom	
	2 ISO25 bottom	
	2 Pg 13 bottom	
	2 Pg 21 bottom	
	2 Pg 16 top	
	2 Pg 16 bottom	
Width	78 mm	
Height	160 mm	
Depth	108 mm	
Net Weight	0.6 kg	

Environment

Material	ABS (acrylonitrile butadiene-styrene)
Ip Degree Of Protection	IP65 conforming to IEC 60529

Excluding VAT and subject to change. Please check with your local distributor through "Where to buy"

Standards	IEC 60947-4-1
	IEC 00947-4-1
Ambient Air Temperature For Operation	-540 °C
Environmental Characteristic	Standard environment
Product Certifications	UKCA

Packing Units

•	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	8.000 cm
Package 1 Width	11.500 cm
Package 1 Length	16.500 cm
Package 1 Weight	572.500 g
Unit Type Of Package 2	S02
Number Of Units In Package 2	6
Package 2 Height	15.000 cm
Package 2 Width	30.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	3.673 kg
Unit Type Of Package 3	P06
Number Of Units In Package 3	96
Package 3 Height	75.000 cm
Package 3 Width	80.000 cm
Package 3 Length	60.000 cm
Package 3 Weight	66.768 kg

Contractual warranty

Warranty

18 months

Sustainability Screen

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Reach Free Of Svhc

S	Toxic Heavy Metal Free	
	Mercury Free	
	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information