Specifications



APC NetShelter SX, Server Rack Enclosure, 42U, Shock Packaging, 2000 lbs, Black, 1991H x 600W x 1070D mm

AR3100SP

Overview	
Presentation	NetShelter SX cabinet and packaging system designed to safely integrate, transport, unload and deploy up to 2000 lbs (907 kg) of IT equipment. The cabinet is paired with a shock absorbing pallet, unloading ramp, and impact resistant shell. The system has been engineered, tested and approved for secure shipment of fully converged systems such as being certified with Cisco® for pre-racking and shipping Cisco Unified Computing System (UCS).
Lead Time	Usually in Stock
Main	
Product Or Component Type	Rack enclosure
Number Of Rack Unit	42U
Provided Equipment	Baying hardware Documentation CD Key(s) Keyed-alike doors and side panels Leveling feet Mounting hardware Pre-installed casters Side panels
Physical	
Height	199.1 cm
Width	60 cm
Depth	107 cm
Net Weight	125.09 kg
Colour	Black
Mounting Preference	No preference
Mounting Mode	Not rack-mountable
Maximum Mounting Depth	91.49 cm
Minimum Mounting Depth	19.1 cm
Rack Width	19"
Marking	14 gauge EIA mounting rail 16 gauge front door 16 gauge post 18 gauge rear door 18 gauge roof 18 gauge side panels
Permanent Permissible Load	1020.58 kg dynamic

Conformance

Excluding VAT and subject to change. Please check with your local distributor through "Where to buy"

1700.97 kg static

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	217.9 cm
Package 1 Width	132.1 cm
Package 1 Length	110.5 cm
Package 1 Weight	242.22 kg

Contractual warranty

Warranty

5 year repair or replace

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Take-back Transparency RoHS/REACh

Resource performance

Take-Back Program Available

Well-being performance

Reach Free Of Svhc

Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile