

Product datasheet

Specifications



APC NetShelter SX, Networking Rack Enclosure, 42U, Grey, 1991H x 750W x 1070D mm

AR3140G

⚠ Discontinued on: 10 Jun 2022

⚠ Discontinued

Overview

Presentation	NetShelter SX Networking Enclosure expands Schneider Electric's superior IT enclosure line with improved support for high density networking applications. Integrated high density cable managers and improved cable access roof provide support for large cable bundles. When combined with the Side Airflow Duct Kit, the Networking Enclosure ensures complete isolation of cold intake and hot exhaust air for large switches and SAN directors.
Lead Time	Usually in Stock

Main

Product Or Component Type	Rack enclosure
Number Of Rack Unit	42U
Provided Equipment	Baying hardware Documentation CD Key(s) Keyed-alike doors and side panels Leveling feet Mounting hardware Pre-installed casters Side panels User manual Vertical cable managers

Physical

Height	199.1 cm
Width	75 cm
Depth	107 cm
Net Weight	155.95 kg
Colour	Grey
Mounting Preference	No preference
Mounting Mode	Not rack-mountable
Mounting Location	Front Rear
Maximum Mounting Depth	81.92 cm
Minimum Mounting Depth	27.94 cm
Rack Width	19"

Excluding VAT and subject to change. Please check with your local distributor through "Where to buy"

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Marking	14 gauge EIA mounting rail 16 gauge front door 16 gauge post 16 gauge rear door 18 gauge roof 18 gauge side panels
Permanent Permissible Load	1020.58 kg dynamic 1700.97 kg static

Conformance

Standards	UL 2416 UL 60950-1 EIA-310E
-----------	-----------------------------------

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	211.8 cm
Package 1 Width	85.09 cm
Package 1 Length	121.9 cm
Package 1 Weight	167.827 kg

Contractual warranty

Warranty	5 year repair or replace
----------	--------------------------

Sustainability





Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.


Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)

Take-back

Transparency


RoHS/REACH

Resource performance



Take-Back Program Available


Well-being performance




Reach Free Of Svhc



Toxic Heavy Metal Free



Mercury Free



Rohs Exemption Information

Yes

Certifications & Standards

Reach Regulation

REACH Declaration

Eu Rohs Directive

Pro-active compliance (Product out of EU RoHS legal scope)

EU RoHS Declaration

Environmental Disclosure

Product Environmental Profile