

Product datasheet

Specifications



BMXFCW303 - Cord set - 40-way terminal - two ends flying leads - for M340 I/O - 3 m

BMXFCW303

Price: 1,874.44 ZAR

Main

Range Of Product	Modicon X80
Accessory / Separate Part Type	Preformed cordset
Accessory / Separate Part Designation	Preformed cordset with one end with flying leads
Accessory / Separate Part Destination	For I/O module with 40-way connectors
Number Of Cables	2
Electrical Connection	1 connector 40 ways 2 ends with color-coded flying leads conforming to DIN 47100
Cable Length	3 m

Complementary

Total Number Of Wires	40
Wire Section	0.324 mm²
Awg Gauge	AWG 22
Net Weight	0.9 kg

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	27.000 cm
Package 1 Width	27.000 cm
Package 1 Length	5.000 cm
Package 1 Weight	885.000 g
Unit Type Of Package 2	S02
Number Of Units In Package 2	5
Package 2 Height	40.000 cm
Package 2 Width	30.000 cm
Package 2 Length	15.000 cm
Package 2 Weight	4.740 kg
Unit Type Of Package 3	P12
Number Of Units In Package 3	288
Package 3 Height	110.000 cm
Package 3 Width	80.000 cm

Excluding VAT and subject to change. Please check with your local distributor through "Where to buy"

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 3 Length	120.000 cm
Package 3 Weight	284.830 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency

Well-being performance

✓ Toxic Heavy Metal Free	
✓ Mercury Free	
✓ Rohs Exemption Information	Yes
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations