# **Product datasheet**

Specifications





## Metal outlet grille cut-out 104x80mm ext dim 120x120mm IP23

NSYCAG170X190LM

#### Price: 200.60 ZAR

#### Main

| Range                                    | ClimaSys                     |
|--|------------------------------|
| Product                                  | ClimaSys CA                  |
| Product Or Component Type                | Metal louvre plate           |
| Accessory / Separate Part<br>Category    | Thermal management accessory |
| Accessory / Separate Part<br>Destination | ClimaSys ventilation system  |
| Mounting Location                        | Sides of enclosure           |
| Fixing Mode                              | By screws                    |
| Device Composition                       | 1 metal louvre               |

## Complementary

| Material                | Steel                  |
|-------------------------|------------------------|
| Colour                  | Grey (RAL 7035)        |
| Surface Finish          | Epoxy-polyester powder |
| Cut-Out Dimensions      | 170 x 190 mm           |
| Height                  | 220 mm external:       |
| Width                   | 220 mm external:       |
| Ip Degree Of Protection | IP23                   |

## **Packing Units**

| Unit Type Of Package 1       | PCE      |
|------------------------------|----------|
| Number Of Units In Package 1 | 1        |
| Package 1 Height             | 1.5 cm   |
| Package 1 Width              | 22 cm    |
| Package 1 Length             | 22 cm    |
| Package 1 Weight             | 617 g    |
| Unit Type Of Package 2       | CAR      |
| Number Of Units In Package 2 | 15       |
| Package 2 Height             | 20 cm    |
| Package 2 Width              | 40 cm    |
| Package 2 Length             | 30 cm    |
| Package 2 Weight             | 10.04 kg |

Excluding VAT and subject to change. Please check with your local distributor through "Where to buy"

| Unit Type Of Package 3       | PAL       |
|------------------------------|-----------|
| Number Of Units In Package 3 | 720       |
| Package 3 Height             | 122.5 cm  |
| Package 3 Width              | 110.5 cm  |
| Package 3 Length             | 123 cm    |
| Package 3 Weight             | 493.92 kg |

### **Contractual warranty**

Warranty

18 months

## Sustainability Screen

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

#### Well-being performance

Mercury Free

Rohs Exemption Information Yes

#### **Certifications & Standards**

| Reach Regulation         | REACh Declaration   |
|--------------------------|---|
| Eu Rohs Directive        | Pro-active compliance (Product out of EU RoHS legal scope)  |
| China Rohs Regulation    | China RoHS declaration<br>Product out of China RoHS scope. Substance declaration for your information |
| Environmental Disclosure | Product Environmental Profile   |
| Circularity Profile      | No need of specific recycling operations  |