

# Product datasheet

Specifications



16 A X/20 A 250 v 1 gang 2 way  
full - flat switch .Silver Bronze

S84312\_SZ

⚠ Discontinued on: 14 Apr 2023

⚠ Discontinued

## Main

Range	ZENcelo
Product Or Component Type	Switch
Device Application	Control
Colour Tint	Silver bronze

## Complementary

Device Mounting	Flush Surface
Switch Function	2-way
Rated Current	20 A/16 AX at 250 V AC 50 Hz
Number Of Gangs	1 gang
Width	50 mm
Height	100 mm

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.5 cm
Package 1 Width	8 cm
Package 1 Length	12.6 cm
Package 1 Weight	165.34 g
Unit Type Of Package 2	CAR
Number Of Units In Package 2	50
Package 2 Height	16 cm
Package 2 Width	37.5 cm
Package 2 Length	79 cm
Package 2 Weight	8539.55 g
Unit Type Of Package 3	PAL
Number Of Units In Package 3	600
Package 3 Height	100 cm
Package 3 Width	80 cm

Excluding VAT and subject to change. Please check with your local distributor through "Where to buy"

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 3 Length	120 cm
Package 3 Weight	99204 g

Sustainability



**Green Premium™ label** is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

✓	Reach Free Of Svhc	
✓	Toxic Heavy Metal Free	
✓	Mercury Free	
✓	Rohs Exemption Information	Yes

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Compliant <a href="#">EU RoHS Declaration</a>
China Rohs Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations