


Product datasheet

Specifications



Actassi CL-MNC6A Patchcord S/FTP 4P Cat6A 550MHz LSZH 1m Grey

VDIP185X46010

⚠ Discontinued on: 15 Dec 2021

⚠ End-of-service on: 31 Dec 2023

⚠ Discontinued

Price: 395.17 ZAR

Main

Range	Actassi
Product	Patch cord
Colour	Patchcord: grey
Quantity Per Set	1
Cable Shielding Type	S/FTP
Provided Component	Grey coloured clips Green coloured clips Red coloured clips

Complementary

Product Compatibility	Coloured clips red Coloured clips green Coloured clips yellow Coloured clips blue
Length (Customizable Value In Configurator)	0...1 m
Communication Network Type	10GBASE-T
Connector Type	RJ45
Communication Network Category	6 _A
Transmission Frequency	550 MHz
Awg Gauge	AWG 26
Input Impedance	100 Ohm
Material	Solid bare copper: conductor PE (polyethylene): wire insulation
Targeted Region	Asia Pacific. Europe

Environment

Ambient Air Temperature For Installation	0...50 °C
Ambient Air Temperature For Operation	-20...60 °C
Ambient Air Temperature For Storage	-20...60 °C
Temperature Resistance	60 °C
Flame Retardance	LSZH

Excluding VAT and subject to change. Please check with your local distributor through "Where to buy"

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Product Certifications	Delta
Standards	IEC 61935-2 ISO/IEC 11801:2011 Ed.2.2 EIA/TIA-568-C.2 EN 50173 Ed.3

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2 cm
Package 1 Width	16 cm
Package 1 Length	20 cm
Package 1 Weight	56 g

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability





Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Well-being performance

	Reach Free Of Svhc	
	Toxic Heavy Metal Free	
	Mercury Free	
	Rohs Exemption Information	Yes
Reach Regulation		REACH Declaration
Eu Rohs Directive		Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation		China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Circularity Profile		No need of specific recycling operations