# **Product datasheet**

Specifications





# Harmony XVR. Rotating beacon. Ø84. red. without buzzer. 24 V AC/ DC

XVR08B04

### Price: 4,418.95 ZAR

### Main

Range Of Product	Harmony XVR
Product Or Component Type	Prewired rotating mirror beacon
Sound Signalling	Without
Device Short Name	XVR
Mounting Diameter	84 mm
Ip Degree Of Protection	IP65 (with accessory) conforming to IEC 60529 IP23 conforming to IEC 60529
[Us] Rated Supply Voltage	24 V AC/DC
Light Source	High luminosity LED, red

### Complementary

Material	ABS (acrylonitrile butadiene-styrene): body part PC: globe	
Cad Overall Width	84 mm	
Cad Overall Depth	84 mm	
Net Weight	0.3 kg	
Marking	CE	
Product Mounting	By 3 M4 screws	
Supply Voltage Limits	1930 V DC 21.626.4 V AC	
[Uimp] Rated Impulse Withstand Voltage	0.8 kV	
Current Consumption	125 mA	
Flashing Frequency	2.3 Hz	
Clamping Connection Capacity	0.83 mm <sup>2</sup>	
Awg Gauge	AWG 18	
Cable Length	500 mm	

# Environment

Standards	IEC 61000-6-4 IEC 61000-6-2
Product Certifications	UL
Protective Treatment	TC
Ambient Air Temperature For Storage	-3570 °C

Excluding VAT and subject to change. Please check with your local distributor through "Where to buy"

Ambient Air Temperature For -1050 °C Operation
---

Electrical Shock Protection Class Class II conforming to IEC 61140

# **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	18.5 cm
Package 1 Width	9.8 cm
Package 1 Length	9.8 cm
Package 1 Weight	395.0 g
Unit Type Of Package 2	\$03
Number Of Units In Package 2	6
Package 2 Height	30.0 cm
Package 2 Width	30.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	3.25 kg

### **Contractual warranty**

Warranty

18 months

# Sustainability Screen Premium

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Yes

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

### Well-being performance

Rohs Exemption Information


### **Certifications & Standards**


Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information

### **Dimensions Drawings**

#### Rotating Mirror Beacon

#### Dimensions





## **Product datasheet**

Mounting and Clearance

#### **Rotating Mirror Beacon**

#### Panel Cut-out

