

Product datasheet

Specifications



circuit breaker Masterpact NW25H1 - 2500 A - 4 poles - drawout - w/o trip unit

48303

Main

Range	MasterPacT
Product Name	MasterPact NW
Circuit Breaker Name	MasterPact NW25H1
Product Or Component Type	Circuit breaker
Device Application	Power distribution protection
Poles Description	4P
Neutral Position	Right
Control Unit	Without control unit
[In] Rated Current	2500 A at 40 °C
Performance Type	H1 65 kA 440 V AC
[Ue] Rated Operational Voltage	690 V AC 50/60 Hz
Suitability For Isolation	Yes conforming to EN/IEC 60947-2
Selectivity Category	Category B
Control Type	Push-button
Mounting Mode	Drawout

Complementary

[Icu] Rated Ultimate Short-Circuit Breaking Capacity	65 kA at 220/415 V AC 50/60 Hz 65 kA at 440 V AC 50/60 Hz 65 kA at 525 V AC 50/60 Hz 65 kA at 690 V AC 50/60 Hz
[Ics] Rated Service Breaking Capacity	65 kA at 220/415 V AC 50/60 Hz 65 kA at 440 V AC 50/60 Hz 65 kA at 525 V AC 50/60 Hz 65 kA at 690 V AC 50/60 Hz
[Icw] Rated Short-Time Withstand Current	65 kA 1 s 65 kA 3 s
[Icm] Rated Short-Circuit Making Capacity	143 kA 220/415 V AC at 50/60 Hz 143 kA 440 V AC at 50/60 Hz 143 kA 525 V AC at 50/60 Hz 143 kA 690 V AC at 50/60 Hz
Sensor Rating	1250 A 2500 A
[Ui] Rated Insulation Voltage	1000 V AC 50/60 Hz
[Uimp] Rated Impulse Withstand Voltage	12 kV
Power Dissipation In W	600 W

Excluding VAT, FCA Jabal Ali & are subject to change – check with your local distributor.

Maximum Breaking Time	25 ms
Maximum Closing Response Time	70 ms
Mounting Support	Backplate Rails
Upside Connection	Front Rear
Downside Connection	Front Rear
Connection Pitch	115 mm
Mechanical Durability	10000 cycles without maintenance 20000 cycles with maintenance
Electrical Durability	5000 cycles 440 V AC 50/60 Hz without maintenance conforming to EN/IEC 60947-2 2500 cycles 690 V AC 50/60 Hz without maintenance conforming to EN/IEC 60947-2 AC-23A: 5000 cycles 440 V AC 50/60 Hz without maintenance conforming to EN/IEC 60947-3 AC-23A: 2500 cycles 690 V AC 50/60 Hz without maintenance conforming to EN/IEC 60947-3 AC-3: 6000 cycles 440/690 V AC 50/60 Hz without maintenance conforming to EN/IEC 60947-3
Height	439 mm
Width	556 mm
Depth	395 mm
Net Weight	120 kg
Standards	EN/IEC 60947-1 EN/IEC 60947-2
Product Certifications	CE CCC EAC

Environment

Ip Degree Of Protection	IP30 conforming to IEC 60529
Pollution Degree	4 conforming to IEC 60664-1
Ambient Air Temperature For Operation	-25...70 °C
Ambient Air Temperature For Storage	-40...85 °C
Operating Altitude	0...2000 m without derating 2000 m...5000 m with derating

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	30.0 cm
Package 1 Width	30.0 cm
Package 1 Length	50.0 cm
Package 1 Weight	38.501 kg

Contractual warranty

Warranty	18 months
-----------------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

Mercury Free

Rohs Exemption Information Yes

Pvc Free

Certifications & Standards

Reach Regulation [REACH Declaration](#)

Eu Rohs Directive Compliant with Exemptions

China Rohs Regulation [China RoHS declaration](#)
Product out of China RoHS scope. Substance declaration for your information

Environmental Disclosure [Product Environmental Profile](#)

Weee The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Circularity Profile [End of Life Information](#)