Product datasheet





PILOT LIGHT 120VAC 30MM **TYPE K +OPTIONS**

9001KP1R9

Main

Range Of Product	Harmony 9001K	
Product Or Component Type	Pilot light	
Device Short Name	9001K	

Complementary

Bezel Material	Metal	
Mounting Diameter	30 mm	
Shape Of Signaling Unit Head	Round	
Lens Type	Domed plastic	
Cap/Operator Or Lens Colour	Red	
Light Source	incandescent	
Bulb Base	BA 9s	
Light Block Supply	Via integral transformer 120 V AC 6 V)	
Connections - Terminals	Screw clamp terminals, 1 x 0.222 x 1.5 mm² conforming to IEC 60947-1	
Tightening Torque	0.8 N.m conforming to IEC 60947-1	
Shape Of Screw Head	Cross slotted	
Shape Of Screw Head	Cross slotted	
Operating Position	Any position	
[Ui] Rated Insulation Voltage	250 V (pollution degree 2) conforming to IEC 60947-1	
[Uimp] Rated Impulse Withstand Voltage	2.5 kV conforming to IEC 60947-1	
Short-Circuit Protection	10 A cartridge fuse conforming to IEC 60947-5-1	
Light Source	Incandescent bulb	
[Ith] Conventional Free Air Thermal Current	10 A	
Cad Overall Width	54 mm	
Cad Overall Height	70 mm	
Cad Overall Depth	42 mm	
[Us] Rated Supply Voltage	110120 V AC	
Net Weight	0.21 kg	
Device Presentation	Complete product	
Lens Type	Domed	
[Us] Rated Supply Voltage	110120 V	

Excluding VAT, FCA Jabal Ali & are subject to change – check with your local distributor.

Light Block Supply	Via integral transformer	
Supply Frequency	5060 Hz	
Lens Material	Polycarbonate	
Size	30 mm	

Environment

Standards	CSA C22.2 No 14 EN/IEC 60947-5-4 EN/IEC 60947-5-1 EN/IEC 60947-1 JIS C 852 JIS C8201-5-1 UL 508 JIS C8201-1	
Product Certifications	NEMA UL 508	
Protective Treatment	тс	
Ambient Air Temperature For Storage	-4070 °C	
Ambient Air Temperature For Operation	-2570 °C	
Vibration Resistance	7 gn (f= 2500 Hz) conforming to IEC 60068-2-6	
Shock Resistance	50 gn conforming to IEC 60068-2-27	
Overvoltage Category	Class II conforming to IEC 61140	
Ip Degree Of Protection	IP66 conforming to IEC 60529	
Nema Degree Of Protection	NEMA 1 NEMA 12 NEMA 13 NEMA 2 NEMA 3 NEMA 3 NEMA 3 NEMA 3R NEMA 4 NEMA 6	

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.572 cm
Package 1 Width	5.588 cm
Package 1 Length	9.398 cm
Package 1 Weight	222.26 g

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Mercury Free



Rohs Exemption Information


Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations

Dimensions Drawings

Dimensions



e panel thickness: 1 to 6 mm / 0.04 to 0.24 in.