Product datasheet

Specification





Acti9 iC60N 1P 63A C Miniature Circuit breaker

A9F44163

Main

Range	Acti9
Product Name	Disbo iC60
Product Or Component Type	Miniature circuit-breaker
Device Short Name	IC60N
Poles Description	1P
Number Of Protected Poles	1
[In] Rated Current	63 A
Network Type	AC
Trip Unit Technology	Thermal-magnetic
Curve Code	С
Breaking Capacity	15 kA Icu at 1260 V DC conforming to EN/IEC 60947-2 10 kA Icu at 6072 V DC conforming to EN/IEC 60947-2 6000 A Icn at 240 V AC 50/60 Hz conforming to EN/IEC 60898-1 36 kA Icu at 1060 V AC 50/60 Hz conforming to EN/IEC 60947-2 20 kA Icu at 100133 V AC 50/60 Hz conforming to EN/IEC 60947-2 10 kA Icu at 220240 V AC 50/60 Hz conforming to EN/IEC 60947-2
Utilisation Category	Category A conforming to FN/IFC 60947-2

Complementary

Network Frequency	50/60 Hz	
[Ue] Rated Operational Voltage	230 V AC 50/60 Hz	
Magnetic Tripping Limit	8 x In +/- 20 %	
[Ics] Rated Service Breaking Capacity	27 kA 75 % conforming to EN/IEC 60947-2 - 1060 V AC 50/60 Hz 15 kA 75 % conforming to EN/IEC 60947-2 - 100133 V AC 50/60 Hz 7.5 kA 75 % conforming to EN/IEC 60947-2 - 220240 V AC 50/60 Hz 6000 A 100 % conforming to EN/IEC 60898-1 - 240 V AC 50/60 Hz 15 kA 100 % conforming to EN/IEC 60947-2 - 1248 V DC 6 kA 100 % conforming to EN/IEC 60947-2 - 72 V DC	
Limitation Class	3 conforming to EN/IEC 60947-2	
[Ui] Rated Insulation Voltage	500 V AC 50/60 Hz	
[Uimp] Rated Impulse Withstand Voltage	6 kV conforming to EN/IEC 60947-2	
Contact Position Indicator	Yes	
Control Type	Toggle	
Local Signalling	Trip indicator	
Mounting Mode	Clip-on	
Mounting Support	Rail	

Excluding VAT, FCA Jabal Ali & are subject to change – check with your local distributor.

9 Mm Pitches	2
Height	85 mm
Width	18 mm
Depth	78.5 mm
Net Weight	0.125 kg
Colour	White
Mechanical Durability	20000 cycles
Electrical Durability	10000 cycles
Provision For Padlocking	Padlockable
Connections - Terminals	Single terminal (top or bottom) 135 mm² rigid Single terminal (top or bottom) 125 mm² flexible
Wire Stripping Length	14 mm for top or bottom connection
Tightening Torque	3.5 N.m top or bottom
Earth-Leakage Protection	Separate block

Environment

Standards	EN/IEC 60947-2 EN/IEC 60898-1
Ip Degree Of Protection	IP20 conforming to IEC 60529
Pollution Degree	3 conforming to EN/IEC 60947-2
Tropicalisation	2 conforming to IEC 60068-1
Relative Humidity	95 % at 55 °C
Ambient Air Temperature For Operation	-3570 °C
Ambient Air Temperature For Storage	-4085 °C

Packing Units

9	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1.9 cm
Package 1 Width	7.2 cm
Package 1 Length	8.9 cm
Package 1 Weight	130 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	12
Package 2 Height	8.5 cm
Package 2 Width	9.7 cm
Package 2 Length	22 cm
Package 2 Weight	1.61 kg
Unit Type Of Package 3	S03
Number Of Units In Package 3	132
Package 3 Height	30 cm
Package 3 Width	30 cm

Package 3 Length	40 cm
Package 3 Weight	18.076 kg

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO2 products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Rohs Exemption Information

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations