Product datasheet

Specifications





Acti9 iC60N 3P 2A C Miniature Circuit breaker

A9F44302

Main

Range	Acti9
Product Name	Disbo iC60
Product Or Component Type	Miniature circuit-breaker
Device Short Name	IC60N
Poles Description	3P
Number Of Protected Poles	3
[In] Rated Current	2 A
Network Type	AC
Trip Unit Technology	Thermal-magnetic
Curve Code	С
Breaking Capacity	50 kA Icu at 220240 V AC 50/60 Hz conforming to EN/IEC 60947-2 50 kA Icu at 12133 V AC 50/60 Hz conforming to EN/IEC 60947-2 50 kA Icu at 380415 V AC 50/60 Hz conforming to EN/IEC 60947-2 25 kA Icu at 440 V AC 50/60 Hz conforming to EN/IEC 60947-2 6000 A Icn at 415 V AC 50/60 Hz conforming to EN/IEC 60898-1 10 kA Icu at <= 180 V DC conforming to EN/IEC 60947-2
Utilisation Category	Category A conforming to FN/IFC 60947-2

Complementary

Network Frequency	50/60 Hz	
[Ue] Rated Operational Voltage	440 V AC 50/60 Hz	
Magnetic Tripping Limit	8 x ln +/- 20 %	
[Ics] Rated Service Breaking Capacity	50 kA 100 % conforming to EN/IEC 60947-2 - 220240 V AC 50/60 Hz 50 kA 100 % conforming to EN/IEC 60947-2 - 12133 V AC 50/60 Hz 50 kA 100 % conforming to EN/IEC 60947-2 - 380415 V AC 50/60 Hz 25 kA 100 % conforming to EN/IEC 60947-2 - 440 V AC 50/60 Hz 6000 A 100 % conforming to EN/IEC 60898-1 - 415 V AC 50/60 Hz 15 kA 100 % conforming to EN/IEC 60947-2 - 100133 V DC	
Limitation Class	3 conforming to EN/IEC 60947-2	
[Ui] Rated Insulation Voltage	500 V AC 50/60 Hz	
[Uimp] Rated Impulse Withstand Voltage	6 kV conforming to EN/IEC 60947-2	
Contact Position Indicator	Yes	
Control Type	Toggle	
Local Signalling	Signalling Trip indicator	
Mounting Mode	Clip-on	
Mounting Support Rail		

Excluding VAT, FCA Jabal Ali & are subject to change – check with your local distributor.

9 Mm Pitches	6
Height	85 mm
Width	54 mm
Depth	78.5 mm
Net Weight	0.375 kg
Colour	White
Mechanical Durability	20000 cycles
Electrical Durability	10000 cycles
Provision For Padlocking	Padlockable
Connections - Terminals	Single terminal (top or bottom) 125 mm² rigid Single terminal (top or bottom) 116 mm² flexible
Wire Stripping Length	14 mm for top or bottom connection
Tightening Torque	2 N.m top or bottom
Earth-Leakage Protection	Separate block

Environment

Standards	EN/IEC 60947-2 EN/IEC 60898-1
Ip Degree Of Protection	IP20 conforming to IEC 60529
Pollution Degree	3 conforming to EN/IEC 60947-2
Tropicalisation	2 conforming to IEC 60068-1
Relative Humidity	95 % at 55 °C
Ambient Air Temperature For Operation	-3570 °C
Ambient Air Temperature For Storage	-4085 °C

Packing Units

9	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	7.5 cm
Package 1 Width	5.4 cm
Package 1 Length	9 cm
Package 1 Weight	331 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	4
Package 2 Height	8.5 cm
Package 2 Width	9.5 cm
Package 2 Length	22 cm
Package 2 Weight	1.387 kg
Unit Type Of Package 3	S03
Number Of Units In Package 3	44
Package 3 Height	30 cm
Package 3 Width	30 cm

Package 3 Length	40 cm
Package 3 Weight	15.966 kg

Sustainability Screen Premium*

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

Mercury Free	
Rohs Exemption Information	Yes
Halogen Free Product	

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations