

# Product datasheet

Specifications



## Fuse carrier TeSys DF, 2P 32A, fuse size 10x38 mm

DF102

Price: 12.70 USD

### Main

Range	TeSys
Product Name	TeSys DF
Product Or Component Type	Fuse carrier
Device Short Name	DF10
Product Compatibility	DF2CA fuse cartridge DF2CN fuse cartridge
Poles Description	2P
Fuse Size	10 x 38 mm
Fuse Type	, aM , gG
Control Type	Toggle padlockable
Utilisation Category	AC-20B conforming to IEC 60947-3 DC-20B conforming to IEC 60947-3
[Ue] Rated Operational Voltage	690 V AC 690 V DC
[Ie] Rated Operational Current	32 A at 400 V AC
[Ith] Conventional Free Air Thermal Current	32 A 20 °C
[Ui] Rated Insulation Voltage	690 V AC
[Uimp] Rated Impulse Withstand Voltage	6 kV
Overvoltage Category	III
Short-Circuit Withstand	120 kA 400 V conforming to IEC 60947-3 120 kA 500 V conforming to IEC 60947-3
Power Dissipation In W	3 W maximum power dissipation by fuse

### Complementary

Standards	EN/IEC 60947-3 EN/IEC 60269-2 UL 4248-1 CSA C22.2 No 4248-1 EN 45545-2: R22 HL2
Product Certifications	IEC UL recognized CSA CCC EAC DNV-GL
Mounting Support	35 mm symmetrical DIN rail
Mounting Position	Vertical (tolerance: +/- 23°)

Excluding VAT, FCA Jabal Ali & are subject to change – check with your local distributor.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Connections - Terminals	Screw clamp terminals 1 cable(s) 1...16 mm²rigid Screw clamp terminals 2 cable(s) 1...6 mm²rigid Screw clamp terminals 1 cable(s) 1...16 mm²flexible with or without Screw clamp terminals 2 cable(s) 1...6 mm²flexible with or without
Tightening Torque	2.2 N.m - with screwdriver PZ2 2.2 N.m - with screwdriver flat Ø 5.5 mm
Height	79.5 mm
Width	35 mm
Depth	61 mm
Net Weight	0.085 kg
Quantity Per Set	Set of 6

## Environment

Ambient Air Temperature For Storage	-40...70 °C
Ambient Air Temperature For Operation	-40...70 °C with derating above 20°C
Operating Altitude	0...2000 m
Ip Degree Of Protection	IP20
Pollution Degree	3
Fire Resistance	960 °C conforming to IEC 60695-2-1
Compatibility Code	DF10

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.5 cm
Package 1 Width	6.2 cm
Package 1 Length	8 cm
Package 1 Weight	90 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	6
Package 2 Height	6.8 cm
Package 2 Width	8.5 cm
Package 2 Length	22.2 cm
Package 2 Weight	566 g
Unit Type Of Package 3	S03
Number Of Units In Package 3	96
Package 3 Height	30 cm
Package 3 Width	30 cm
Package 3 Length	40 cm
Package 3 Weight	9.66 kg

## Contractual warranty

Warranty	18 months
----------	-----------

Sustainability



**Green Premium™ label** is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

✓	Reach Free Of Svhc	
✓	Toxic Heavy Metal Free	
✓	Mercury Free	
✓	Rohs Exemption Information	Yes

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Compliant <a href="#">EU RoHS Declaration</a>
China Rohs Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations <a href="#">Circularity Profile</a>