Product datasheet

Specifications





16AX 250V 1Gang Intermediate switched with Fluorescent Locator, Aluminium Silver

E8231MF_AS_G1

Main

Range	Pieno	
Product Or Component Type	Switch	
Device Application	Control	
Switch Application	Switch	
Load Type	Resistive Fluorescent	
Cover Frame Colour Tint	Aluminium silver	

Complementary

Device Mounting	Surface Flush	
Wiring Device Mounting	Surface Flush	
Switch Function	2-way	
Rated Current	16 AX at 250 V AC 50 Hz	
Local Signalling	Fluorescent (white)	
Number Of Gangs	1 gang	
Material	Polycarbonate: surround Polycarbonate: grid plate	
Connections - Terminals	Pillar terminals	
Clamping Connection Capacity	2 x 1.5 mm² for stranded cable(s) 2 x 2.5 mm² for solid cable(s)	
Embedding Depth	23 mm	
Width	87 mm	
Height	87 mm	
Depth	23 mm	

Environment

Ambient Air Temperature For Operation	-540 °C
Relative Humidity	095 %
Standards	GB 16915.1 MS IEC 60669-1 IEC 60669-1 SS 227-1 BS EN 60669-1

Excluding VAT, FCA Jabal Ali & are subject to change – check with your local distributor.

Packing Units



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

②	Reach Free Of Svhc	
②	Toxic Heavy Metal Free	
②	Mercury Free	
⊘	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations