Product datasheet

Specifications





Pieno - 1 gang TV socket master - 75 Ohm - 5-860 MHz (MB)

E8231TV_MB

Main

Range Of Product	Pieno
Product Or Component Type	TV/FM/SAT socket
Tv Socket Type	TV
Number Of Gangs	1 gang

Complementary

Wiring Device Mounting	Flush
Average Impedance	75 Ohm
Material	Polycarbonate: surround Polycarbonate: grid plate
Bandwidth	5860 Hz TV
Connections - Terminals	IEC connection Clamp terminal
Width	87 mm
Height	87 mm

Environment

Ambient Air Temperature For Operation	-540 °C
Relative Humidity	095 %
Standards	IEC 60670 GB 17466

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.8 cm
Package 1 Width	8.6 cm
Package 1 Length	8.6 cm
Package 1 Weight	64.5 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	10
Package 2 Height	9.5 cm
Package 2 Width	19.0 cm

Excluding VAT, FCA Jabal Ali & are subject to change – check with your local distributor.

Package 2 Length	19.5 cm
Package 2 Weight	741.0 g
Unit Type Of Package 3	CAR
Number Of Units In Package 3	60
Package 3 Height	21.0 cm
Package 3 Width	30.0 cm
Package 3 Length	39.5 cm
Package 3 Weight	4.926 kg



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

Reach Free Of Svhc

Mercury Free

Rohs Exemption Information

Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations