Product datasheet

Specifications





Pieno - 10A 250V - 1 gang bell press switch with fluorescent locator (MB)

E8231BPL1_MB

Main

| Range Of Product | Pieno | |
|---------------------------|------------------------|--|
| Product Or Component Type | Switch | |
| Switch Function | Momentary | |
| Switch Application | Bell | |
| Rated Current | 10 A at 250 V AC 50 Hz | |
| Local Signalling | Fluorescent (white) | |
| Number Of Gangs | 1 gang | |
| Load Type | Resistive | |

Complementary

| Wiring Device Mounting | Flush Surface |
|------------------------------|---------------------------------------------------------------------|
| Material | Polycarbonate: surround Polycarbonate: grid plate |
| Connections - Terminals | Pillar terminals |
| Clamping Connection Capacity | 2 x 1.5 mm² for stranded cable(s) 2 x 2.5 mm² for solid cable(s) |
| Width | 87 mm |
| | 87 mm |

Environment

| Ambient Air Temperature For Operation | -540 °C |
|------------------------------------------|---------------------------|
| Relative Humidity | 095 % |
| Standards | GB 16915.1 IEC 60669-1 |
| Product Certifications | ccc |

Packing Units

| Unit Type Of Package 1 | PCE |
|------------------------------|---------|
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 3.3 cm |
| Package 1 Width | 8.6 cm |
| Package 1 Length | 8.6 cm |
| Package 1 Weight | 155.8 g |

Excluding VAT, FCA Jabal Ali & are subject to change – check with your local distributor.



Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

| ⊘ | Reach Free Of Svhc | |
|----------|----------------------------|-----|
| ② | Toxic Heavy Metal Free | |
| 9 | Mercury Free | |
| ⊘ | Rohs Exemption Information | Yes |

Certifications & Standards

| Reach Regulation | REACh Declaration |
|--------------------------|-----------------------------------------------------------------------------------------------------|
| Eu Rohs Directive | Compliant with Exemptions |
| China Rohs Regulation | China RoHS declaration Product out of China RoHS scope. Substance declaration for your information |
| Environmental Disclosure | Product Environmental Profile |
| Circularity Profile | No need of specific recycling operations |