Product datasheet

Specification





10A Mechanical Curtain switched with Fluorescent Locator, Wine Gold

E8231CF_WG_G1

Main

Range	Pieno
Device Application	Control
Product Or Component Type	Dimmer
[Ue] Rated Operational Voltage	250 V AC 50 Hz
Number Of Gangs	1 gang
Cover Frame Colour Tint	Wine gold

Complementary

Wiring Device Mounting	Surface Flush
Width	87 mm
Height	87 mm
Depth	47 mm
Rated Current	10 A
Connections - Terminals	Pillar terminals

Environment

Ambient Air Temperature For Operation	-540 °C
Relative Humidity	095 %
Standards	IEC 60669

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.55 cm
Package 1 Width	8.7 cm
Package 1 Length	8.7 cm
Package 1 Weight	98.58 g
Unit Type Of Package 2	CAR
Number Of Units In Package 2	60
Package 2 Height	21 cm
Package 2 Width	32.5 cm

Excluding VAT, FCA Jabal Ali & are subject to change – check with your local distributor.

Package 2 Length	50 cm
Package 2 Weight	5914.8 g
Unit Type Of Package 3	PAL
Number Of Units In Package 3	1200
Package 3 Height	84 cm
Package 3 Width	82.5 cm
Package 3 Length	100 cm
Package 3 Weight	135296 g



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

⊘	Reach Free Of Svhc	
9	Toxic Heavy Metal Free	
②	Mercury Free	
⊘	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations