Product datasheet

Specifications





450W 240V 1 Gang Dimmer with Switch, Lavendar Silver

E8232RD450U_WG_G1

Main

Range	Pieno
Product Or Component Type	Dimmer
Power Range	450 W LV halogen
Device Application	Load control
[Ue] Rated Operational Voltage	250 V AC 50 Hz
Number Of Gangs	1 gang

Complementary

Wiring Device Mounting	Surface Flush
Connections - Terminals	Pillar terminals
Width	87 mm
Height	87 mm
Depth	47 mm

Environment

Ambient Air Temperature For Operation	-540 °C
Relative Humidity	095 %
Standards	IEC 60669

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5.35 cm
Package 1 Width	8.7 cm
Package 1 Length	8.7 cm
Package 1 Weight	104.53 g
Unit Type Of Package 2	CAR
Number Of Units In Package 2	60
Package 2 Height	21 cm
Package 2 Width	32.5 cm
Package 2 Length	50 cm

Excluding VAT, FCA Jabal Ali & are subject to change – check with your local distributor.

Package 2 Weight	6271.8 g
Unit Type Of Package 3	PAL
Number Of Units In Package 3	1200
Package 3 Height	84 cm
Package 3 Width	82.5 cm
Package 3 Length	100 cm
Package 3 Weight	142436 g



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations