

Product datasheet

Specifications



45A 250V Double Pole Sw with Neon + 13A Sw Socket with Neon, Aluminium Silver

E82T15D45N_AS_G1

⚠ Discontinued on: 17 Jul 2023

⚠ Discontinued

Main

Range	Pieno
Product Or Component Type	Cooker control unit socket
Device Application	Control
Load Type	Fluorescent Resistive
Cover Frame Colour Tint	Aluminium silver

Complementary

Device Mounting	Surface Flush
Wiring Device Mounting	Surface Flush
Rated Current	45 A at 250 V AC 50 Hz
Local Signalling	Neon
Number Of Gangs	1 gang
Material	Polycarbonate: surround Polycarbonate: grid plate
Connections - Terminals	Folded terminal Pillar terminals
Clamping Connection Capacity	3 x 2.5 mm ² for solid cable(s) 1 x 10 mm ² for stranded cable(s)
Embedding Depth	24.5 mm
Width	147 mm
Height	87 mm
Depth	34.1 mm

Environment

Ambient Air Temperature For Operation	-5...40 °C
Relative Humidity	0...95 %
Standards	BS 4177

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1

Excluding VAT, FCA Jabal Ali & are subject to change – check with your local distributor.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Height	3.41 cm
Package 1 Width	8.7 cm
Package 1 Length	14.7 cm
Package 1 Weight	237.03 g
Unit Type Of Package 2	CAR
Number Of Units In Package 2	50
Package 2 Height	21 cm
Package 2 Width	32.5 cm
Package 2 Length	50 cm
Package 2 Weight	11851.5 g
Unit Type Of Package 3	PAL
Number Of Units In Package 3	1000
Package 3 Height	84 cm
Package 3 Width	82.5 cm
Package 3 Length	100 cm
Package 3 Weight	254030 g

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓	Reach Free Of Svhc	
✓	Toxic Heavy Metal Free	
✓	Mercury Free	
✓	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations