

Product datasheet

Specifications



Pieno - 1 gang TV socket master - 75 Ohm - 5-860 MHz (MB)

E8231TV_MB

Main

Range of product	Pieno
Product or component type	TV/FM/SAT socket
TV socket type	TV
Number of gangs	1 gang

Complementary

Wiring device mounting	Flush
Average impedance	75 Ohm
Material	Polycarbonate: surround Polycarbonate: grid plate
Bandwidth	5...860 Hz TV
Connections - terminals	IEC connection Clamp terminal
Width	87 mm
Height	87 mm

Environment

Ambient air temperature for operation	-5...40 °C
Relative humidity	0...95 %
Standards	IEC 60670 GB 17466

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	64.5 g
Package 1 Height	2.8 cm
Package 1 Width	8.6 cm
Package 1 Length	8.6 cm
Unit Type of Package 2	BB1
Number of Units in Package 2	10

Package 2 Weight	741.0 g
Package 2 Height	9.5 cm
Package 2 Width	19 cm
Package 2 Length	19.5 cm
Unit Type of Package 3	CAR
Number of Units in Package 3	60
Package 3 Weight	4.926 kg
Package 3 Height	21 cm
Package 3 Width	30 cm
Package 3 Length	39.5 cm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile

Recommended replacement(s)