

Product datasheet

Specifications



10AX 250V 4 Gang 1 Way Switch with Neon, White

E8234L1N_WE

⚠ Discontinued on: 30 Jun 2023

⚠ Discontinued

Main

Range	Pieno
Product Or Component Type	Switch
Switch Application	Switch
Load Type	Fluorescent Resistive
Cover Frame Colour Tint	White

Complementary

Device Mounting	Surface Flush
Wiring Device Mounting	Flush Surface
Switch Function	1-way
Rated Current	10 AX at 250 V AC 50 Hz
Local Signalling	Neon
Number Of Gangs	4 gangs
Material	Polycarbonate: surround Polycarbonate: grid plate
Connections - Terminals	Pillar terminals
Clamping Connection Capacity	2 x 2.5 mm² for solid cable(s) 3 x 1.5 mm² for stranded cable(s)
Embedding Depth	23 mm
Width	87 mm
Height	87 mm
Depth	35.5 mm

Environment

Ambient Air Temperature For Operation	-5...40 °C
Relative Humidity	0...95 %
Standards	IEC 60669-1 GB 16915.1 MS IEC 60669-1 BS EN 60669-1 SS 227-1

Excluding VAT, FCA Jabal Ali & are subject to change – check with your local distributor.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.6 cm
Package 1 Width	8.7 cm
Package 1 Length	8.7 cm
Package 1 Weight	149 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	6
Package 2 Height	9.5 cm
Package 2 Width	15 cm
Package 2 Length	19 cm
Package 2 Weight	772.38 g
Unit Type Of Package 3	CAR
Number Of Units In Package 3	60
Package 3 Height	21 cm
Package 3 Width	32.5 cm
Package 3 Length	50 cm
Package 3 Weight	7251.9 g

Contractual warranty

Warranty	18 months
----------	-----------