## **Product datasheet**

Specifications



# 45A connection unit White Plate+White Surround

E84554-WW

() Discontinued on: 20 Jun 2023

#### Main

Range	ZENcelo
Product Or Component Type	Connection unit
Colour Tint	White
Load Type	Resistive Inductive
Cover Frame Colour Tint	White

#### Complementary

Width	87 mm
Height	87 mm
Depth	30 mm
Wiring Device Mounting	Surface Flush
Rated Current	25 A at 250 V AC 50 Hz
Material	Polycarbonate + 20 % FG: grid plate Polycarbonate: base Polycarbonate: surround
Contacts Material	Contact: brass and phosphor bronze
Connections - Terminals	Pillar terminals
Number Of Cables	1 cable(s) 16 mm <sup>2</sup>

#### Environment

Ambient Air Temperature For Operation	-540 °C
Relative Humidity	095 %
Environmental Characteristic	UV resistant indoor use
Operating Altitude	2000 m
Standards	BS 5733

#### **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	8.7 cm
Package 1 Width	8.7 cm

Excluding VAT, FCA Jabal Ali & are subject to change - check with your local distributor.

Package 1 Length	3 cm
Package 1 Weight	0.001 g

### Sustainability Screen Premium

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Yes

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

#### Well-being performance

Mercury Free

Rohs Exemption Information

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations