Product datasheet

Specification





Easy9 switch disconnector - 4P - 125 A - 400 V

EZ9S16492

Main

Range	Easy9	
Product Or Component Type	Switch	
Device Short Name	Easy9 switch	
Switch Application	Distribution	
Poles	4P	
Utilisation Category	AC-22A	
Suitability For Isolation	Yes	

Complementary

<u> </u>		
[le] Rated Operational Current	125 A at 400 V 50/60 Hz	
[Ue] Rated Operational Voltage	400 V AC 50/60 Hz	
[Icm] Rated Short-Circuit Making Capacity	1.875 kA	
[Icw] Rated Short-Time Withstand Current	1.5 kA during 1 s	
[Ui] Rated Insulation Voltage	500 V AC 50/60 Hz	
[Uimp] Rated Impulse Withstand Voltage	4 kV	
Control Type	Toggle	
Local Signalling	ON/OFF indication	
Contact Position Indicator	Yes	
Mounting Mode	Clip-on	
Mounting Support	DIN rail	
9 Mm Pitches	8	
Height	81 mm	
Width	72 mm	
Depth	66.5 mm	
Colour	Grey	
Mechanical Durability	7000 cycles	
Electrical Durability	1000 cycles	
Connections - Terminals	Tunnel type terminal (top or bottom) 150 mm² rigid Tunnel type terminal (top or bottom) 135 mm² flexible	
Tightening Torque	3.5 N.m	

Environment

Excluding VAT, FCA Jabal Ali & are subject to change – check with your local distributor.

Standards	IEC 60947-3	
Product Certifications	CE	
Ip Degree Of Protection	IP20 conforming to IEC 60529	
Tropicalisation	2	
Ambient Air Temperature For Operation	-555 °C	
Ambient Air Temperature For Storage	-570 °C	

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	7.75 cm
Package 1 Width	7.21 cm
Package 1 Length	8.55 cm
Package 1 Weight	365.0 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	3
Package 2 Height	8.2 cm
Package 2 Width	8.8 cm
Package 2 Length	22.3 cm
Package 2 Weight	1.09 kg
Unit Type Of Package 3	S03
Number Of Units In Package 3	36
Package 3 Height	30.0 cm
Package 3 Width	30.0 cm
Package 3 Length	40.0 cm
Package 3 Weight	13.14 kg



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

⊘	Reach Free Of Svhc	
⊘	Toxic Heavy Metal Free	
⊘	Mercury Free	
⊘	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations