Product datasheet

Specifications





LADN22 Auxiliary contact block, TeSys D, 2NO + 2NC, front mounting, screw terminals. As the best selling line of contactors in the world, TeSys D offers multistandard solutions, high reliability with long mechanical and electrical durability for different sizes, along with the most complete accessories in the industry.

LADN22

Price: 23.41 USD

Main

Range	TeSys TeSys Deca	
Product Name	TeSys Deca	
Product Or Component Type	Auxiliary contact block	
Device Short Name	LADN	
Range Compatibility	TeSys D CAD TeSys D LC1D TeSys F LC1F TeSys F CR1F TeSys Deca CAD TeSys Deca LC1D	
Mounting Location	Front	
Pole Contact Composition	entact Composition 2 NO + 2 NC	
Contacts Operation	Instantaneous	
[Ue] Rated Operational Voltage	690 V AC 25400 Hz	
[le] Rated Operational Current	6 A at 120 V AC-15 1.04 A at 690 V AC-15 0.55 A at 125 V DC-13 0.1 A at 600 V DC-13	
[Ui] Rated Insulation Voltage	690 V conforming to IEC 60947-5-1 600 V conforming to UL 600 V conforming to CSA	
[Ith] Conventional Free Air Thermal Current	10 A (at 60 °C)	
Standards	EN/IEC 60947-5-1 GB/T 14048.5	
Product Certifications	CB UL CSA CCC UKCA	

Complementary

Excluding VAT, FCA Jabal Ali & are subject to change – check with your local distributor.

Irms Rated Making Capacity	440.4.40. a confermina to IEO 00047.5.4
irms Rated Making Capacity	140 A AC conforming to IEC 60947-5-1
	250 A DC conforming to IEC 60947-5-1
Permissible Short-Time Rating	100 A 60 °C 1 s
	120 A 60 °C 500 ms
	140 A 60 °C 100 ms
Protection Type	GG fuse 10 A
Mechanical Durability	30 Mcycles
Minimum Switching Current	5 mA
Minimum Switching Voltage 17 ∨	
Non-Overlap Time	1.5 ms on de-energisation no overlap between NC and NO contact
•	1.5 ms on energisation no overlap between NC and NO contact
Insulation Resistance > 10 MOhm	
Connections - Terminals	Screw clamp terminals 1 cable(s) 14 mm²flexible with cable end
	Screw clamp terminals 1 cable(s) 14 mm²flexible without cable end
	Screw clamp terminals 2 cable(s) 12.5 mm²flexible with cable end
	Screw clamp terminals 2 cable(s) 14 mm²flexible without cable end
	Screw clamp terminals 1 cable(s) 14 mm²rigid without cable end
	Screw clamp terminals 2 cable(s) 14 mm²rigid without cable end
Tightening Torque	1.7 N.m - with screwdriver flat Ø 6 mm
	1.7 N.m - with screwdriver Philips No 2
	1.7 N.m - with screwdriver pozidriv No 2
Height	48 mm
Width	44 mm
Depth	42 mm
Net Weight	0.05 kg
Colour Dark grey	

Environment

Environmental Characteristic	Normal environment	
Ip Degree Of Protection	IP20 conforming to IEC 60529	
Protective Treatment	TH conforming to IEC 60068	
Ambient Air Temperature For Storage	-6080 °C	
Ambient Air Temperature For Operation	-560 °C	
Operating Altitude	3000 m	

Packing Units

Unit Type Of Package 1	PCE	
Number Of Units In Package 1	1	
Package 1 Height	5.000 cm	
Package 1 Width	5.000 cm	
Package 1 Length	4.400 cm	
Package 1 Weight	62.000 g	
Unit Type Of Package 2	S03	
Number Of Units In Package 2	160	
Package 2 Height	30.000 cm	
Package 2 Width	30.000 cm	

Package 2 Length	40.000 cm	
Package 2 Weight	10.470 kg	
Unit Type Of Package 3	P06	
Number Of Units In Package 3	1280	
Package 3 Height	75.000 cm	
Package 3 Width	60.000 cm	
Package 3 Length	Length 80.000 cm	
Package 3 Weight	91.760 kg	

Sustainability Green Premium

Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

②	Reach Free Of Svhc	
9	Toxic Heavy Metal Free	
⊘	Mercury Free	
⊘	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations