Product datasheet

Specifications





EasyPact TVS contactor 3P(3 NO) - AC-3 - <= 440 V 50A - 220 V AC coil

LC1E50M5

Main

Range	Easy TeSys	
Range Of Product	Easy TeSys Control	
Product Or Component Type	Contactor	
Device Short Name	LC1E	
Contactor Application	Resistive load Motor control	
Utilisation Category	AC-1 AC-3	
Poles Description	3P	
[Ue] Rated Operational Voltage	Power circuit: <= 690 V AC 50/60 Hz	
[le] Rated Operational Current	50 A (at <55 °C) at <= 440 V AC AC-3 for power circuit 70 A (at <55 °C) at <= 440 V AC AC-1 for power circuit	
[Uc] Control Circuit Voltage	220 V AC 50 Hz	

Complementary

Motor Power Kw	15 kW at 220230 V AC 50/60 Hz (AC-3)
	22 kW at 380400 V AC 50/60 Hz (AC-3)
	25 kW at 415 V AC 50/60 Hz (AC-3)
	30 kW at 440 V AC 50/60 Hz (AC-3)
	30 kW at 500 V AC 50/60 Hz (AC-3)
	33 kW at 660690 V AC 50/60 Hz (AC-3)
Pole Contact Composition	3 NO
[Ith] Conventional Free Air Thermal Current	70 A (at 55 °C)
Irms Rated Making Capacity	500 A at 440 V AC for power circuit conforming to IEC 60947-4-1
Rated Breaking Capacity	400 A at 440 V for power circuit conforming to IEC 60947
[Icw] Rated Short-Time Withstand	400 A 40 °C - 10 s for power circuit
Current	208 A 40 °C - 60 s for power circuit
	84 A 40 °C - 600 s for power circuit
Associated Fuse Rating	10 A gG at <= 690 V coordination type 1 for control circuit conforming to IEC
	60947-5-1
	100 A gG at <= 690 V coordination type 1 for power circuit
Average Impedance	1.5 mOhm - Ith 70 A 50 Hz for power circuit
Power Dissipation Per Pole	3.8 W AC-3
	7.4 W AC-1
[Ui] Rated Insulation Voltage	690 V conforming to IEC 60947-4-1
Overvoltage Category	III
Pollution Degree	3

Excluding VAT, FCA Jabal Ali & are subject to change - check with your local distributor.

[Uimp] Rated Impulse Withstand Voltage	6 kV coil not connected to the power circuit conforming to IEC 60947
Mechanical Durability	5000000 cycles
Electrical Durability	350000 cycles AC-1 900000 cycles AC-3
Control Circuit Type	AC at 50 Hz
Control Circuit Voltage Limits	0.851.1 Uc (-555 °C):operational 50 Hz 0.30.6 Uc (-555 °C):drop-out 50 Hz
Inrush Power In Va	160 VA 50 Hz cos phi 0.75 (at 20 °C) 140 VA 60 Hz cos phi 0.75 (at 20 °C)
Hold-In Power Consumption In Va	15 VA 50 Hz cos phi 0.3 (at 20 °C) 13 VA 60 Hz cos phi 0.3 (at 20 °C)
Heat Dissipation	610 W for control circuit
Operating Time	2026 ms on closing 812 ms on opening
Maximum Operating Rate	1200 cyc/h 60 °C
Connections - Terminals	Control circuit: screw clamp terminals 1 14 mm ² - cable stiffness: flexible without cable end Control circuit: screw clamp terminals 2 14 mm ² - cable stiffness: flexible without cable end Control circuit: screw clamp terminals 1 14 mm ² - cable stiffness: flexible with cable end Control circuit: screw clamp terminals 2 12.5 mm ² - cable stiffness: flexible with cable end Control circuit: screw clamp terminals 1 14 mm ² - cable stiffness: solid without cable end Control circuit: screw clamp terminals 1 14 mm ² - cable stiffness: solid without cable end Control circuit: screw clamp terminals 2 125 mm ² - cable stiffness: solid without cable end Power circuit: screw clamp terminals 2 14 mm ² - cable stiffness: solid without cable end Power circuit: screw clamp terminals 1 2.525 mm ² - cable stiffness: flexible with cable end Power circuit: screw clamp terminals 2 2.510 mm ² - cable stiffness: solid without cable end Power circuit: screw clamp terminals 1 2.525 mm ² - cable stiffness: solid without cable end Power circuit: screw clamp terminals 2 2.510 mm ² - cable stiffness: solid without cable end Power circuit: screw clamp terminals 2 2.510 mm ² - cable stiffness: solid without cable end Power circuit: screw clamp terminals 2 2.516 mm ² - cable stiffness: solid without cable end
Tightening Torque	Control circuit: 1.2 N.m Power circuit: 5 N.m
Auxiliary Contact Composition	1 NO + 1 NC
Minimum Switching Voltage	17 V for control circuit
Minimum Switching Current	5 mA for control circuit
Insulation Resistance	> 10 MOhm for control circuit
Non-Overlap Time	1.5 ms on energisation guaranteed between NC and NO contact 1.5 ms on de-energisation guaranteed between NC and NO contact
Mounting Support	Plate DIN rail

Environment

Standards	IEC 60947-1 IEC 60947-5-1 IEC 60947-4-1	
Product Certifications	EAC CE	
Ip Degree Of Protection	IP2X conforming to IEC 60529	
Protective Treatment	TH (pollution degree 3) conforming to IEC 60068-2-30 test Db	

Permissible Ambient Air Temperature Around The Device	-2070 °C at Uc -6080 °C storage -555 °C operation	
Operating Altitude	3000 m without derating	
Fire Resistance	850 °C conforming to IEC 60695-2-1	
Mechanical Robustness	Vibrations contactor open (1.5 Gn, 5300 Hz) Vibrations contactor closed (3 Gn, 5300 Hz) Shocks contactor open (6 Gn for 11 ms) Shocks contactor closed (7 Gn for 11 ms)	
Height	127 mm	
Width	75 mm	
Depth	114 mm	
Net Weight	0.98 kg	

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	12.200 cm
Package 1 Width	8.200 cm
Package 1 Length	13.300 cm
Package 1 Weight	975.000 g
Unit Type Of Package 2	S02
Number Of Units In Package 2	9
Package 2 Height	15.000 cm
Package 2 Width	30.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	9.141 kg

Contractual warranty

Warranty

18 months

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Reach Free Of Svhc
Toxic Heavy Metal Free
Mercury Free
Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information