Product datasheet

Specification





Enclosed DOL starter, TeSys LE, 9A,400V AC coil, including 1 LC1D, 2 pushbuttons

LE1D09V7

Main

| Range | TeSys |
|---------------------------|---|
| Product Name | TeSys LE |
| Device Short Name | LE1D |
| Product Or Component Type | Enclosed DOL starter |
| Device Application | Standard |
| Utilisation Category | AC-3 |
| Device Composition | Thermal overload relay ordered separately Contactor |
| Control Type | Push-button start green I |

Complementary

| Motor Power Kw | 4 kW at 380/400 V AC 50/60 Hz 4 kW at 415 V AC 50/60 Hz 4 kW at 440 V AC 50/60 Hz 2.2 kW at 220/230 V AC 50/60 Hz 5.5 kW at 500 V AC 50/60 Hz 5.5 kW at 660/690 V AC 50/60 Hz |
|--|--|
| | 3.5 KW at 000/030 V AC 30/00 Hz |
| [Ith] Conventional Free Air Thermal Current | 9 A |
| [Uc] Control Circuit Voltage | 400 V AC 50/60 Hz |
| Cable Entry Number | 2 ISO20 top 2 ISO20 bottom |
| Width | 88 mm |
| Height | 166 mm |
| Depth | 128.5 mm |
| Net Weight | 0.92 kg |

Environment

| Material | Polycarbonate |
|--|------------------------------|
| Ip Degree Of Protection | IP65 conforming to IEC 60529 |
| Ik Degree Of Protection | IK07 conforming to IEC 60529 |
| Standards | IEC 60947-4-1 |
| Ambient Air Temperature For Operation | -540 °C |
| Environmental Characteristic | Standard environment |
| Product Certifications | UKCA |

Excluding VAT, FCA Jabal Ali & are subject to change – check with your local distributor.

Packing Units

| Unit Type Of Package 1 | PCE |
|------------------------------|----------|
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 19.5 cm |
| Package 1 Width | 20.0 cm |
| Package 1 Length | 25.5 cm |
| Package 1 Weight | 874.0 g |
| Unit Type Of Package 2 | P06 |
| Number Of Units In Package 2 | 30 |
| Package 2 Height | 80.0 cm |
| Package 2 Width | 80.0 cm |
| Package 2 Length | 60.0 cm |
| Package 2 Weight | 39.22 kg |

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

| ⊘ | Reach Free Of Svhc | |
|----------|----------------------------|-----|
| 9 | Toxic Heavy Metal Free | |
| ② | Mercury Free | |
| ⊘ | Rohs Exemption Information | Yes |

Certifications & Standards

| Reach Regulation | REACh Declaration |
|---------------------------------|---|
| Eu Rohs Directive | Compliant EU RoHS Declaration |
| China Rohs Regulation | China RoHS declaration |
| Environmental Disclosure | Product Environmental Profile |
| Weee | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins |
| Circularity Profile | End of Life Information |