Product datasheet

Specifications





() Discontinued

LR9F5369 TeSys LRF - electronic thermal overload relay - 90...150 A - class 10. 3 complete offers of electronic thermal overload relays for advanced motor protection. TeSys LR9 – LR9D / LR9D.

LR9F5369

() Discontinued on: 26 Sep 2023

Main

in entre	
Range	TeSys
Product Name	TeSys LRF
Device Short Name	LR9F
Product Or Component Type	Electronic thermal overload relay
Relay Application	Motor protection
Product Compatibility	LC1F115LC1F185
Network Type	AC
Thermal Overload Class	Class 10 conforming to IEC 60947-4
Thermal Protection Adjustment Range	90150 A

Complementary

Network Frequency	50/60 Hz	
Mounting Support	Direct on contactor Plate	
Tripping Threshold	1.12 +/- 0.06 In tripping conforming to IEC 60947-4-1	
Surge Withstand	4 kV conforming to IEC 61000-4-5	
Contacts Type And Composition	1 NO + 1 NC	
[Ith] Conventional Free Air Thermal Current	5 A for control circuit	
[Ue] Rated Operational Voltage	1000 V AC 50/60 Hz for power circuit conforming to VDE 0110 group C	
[Ui] Rated Insulation Voltage	Power circuit: 1000 V AC conforming to IEC 60947-4	
[Uimp] Rated Impulse Withstand Voltage	8 kV conforming to IEC 60947-1	
Phase Failure Sensitivity	Tripping in 4 s +/- 20 % conforming to IEC 60947-4-1	
Reset	Manual reset on front relay	
Control Type	Dial white full-load current adjustment Test button red Push-button red reset Push-button stop	
Local Signalling	Trip indicator	
Temperature Compensation	-2070 °C	

Excluding VAT, FCA Jabal Ali & are subject to change - check with your local distributor.

Current Consumption	<= 5 mA no-load
Switching Capacity For Alarm	0150 mA
Maximum Voltage Drop	<2.5 V closed state
Connections - Terminals	Control circuit: screw clamp terminals 1 cable 0.752.5 mm ² - cable stiffness: flexible - with cable end Control circuit: screw clamp terminals 1 cable 0.752.5 mm ² - cable stiffness: solid Control circuit: screw clamp terminals 1 cable 0.754 mm ² - cable stiffness: flexible - without cable end Control circuit: screw clamp terminals 2 cable 11.5 mm ² - cable stiffness: flexible - with cable end Control circuit: screw clamp terminals 2 cable 12.5 mm ² - cable stiffness: flexible - with cable end Control circuit: screw clamp terminals 2 cable 12.5 mm ² - cable stiffness: flexible - without cable end Control circuit: screw clamp terminals 2 cable 12.5 mm ² - cable stiffness: solid Power circuit: lugs-ring terminals M8
Tightening Torque	Control circuit: 1.2 N.m on screw clamp terminals Power circuit: 18 N.m on screw clamp terminals
Height	96 mm
Width	115 mm
Depth	123.5 mm
Net Weight	0.885 kg

Environment

Standards	VDE 0660 IEC 60255-17 IEC 60947-4-1 IEC 60255-8 EN 60947-4-1
Product Certifications	UL CSA UKCA
Protective Treatment	тн
Ip Degree Of Protection	IP20 conforming to IEC 60529 IP20 conforming to VDE 0106
Ambient Air Temperature For Operation	-2055 °C conforming to IEC 60255-8
Ambient Air Temperature For Storage	-4085 °C
Operating Altitude	<= 2000 m without derating
Fire Resistance	850 °C conforming to IEC 60695-2-1
Mechanical Robustness	Shocks: 13 Gn for 11 ms conforming to IEC 60068-2-7 Vibrations 5300 Hz: 2 GN conforming to IEC 60068-2-6
Dielectric Strength	6 kV 50 Hz conforming to IEC 255-5
Electromagnetic Compatibility	Resistance to electrostatic discharge: 6 kV in indirect mode conforming to IEC 61000-4-2 Resistance to electrostatic discharge: 8 kV in air conforming to IEC 61000-4-2 Radiated radio-frequency electromagnetic field immunity test: 10 V/m conforming to IEC 61000-4-3 Fast transients immunity test: 2 kV conforming to IEC 61000-4-4

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	15.000 cm
Package 1 Width	16.000 cm
Package 1 Length	13.600 cm

Package 1 Weight	866.000 g
Unit Type Of Package 2	S04
Number Of Units In Package 2	12
Package 2 Height	30.000 cm
Package 2 Width	40.000 cm
Package 2 Length	60.000 cm
Package 2 Weight	11.300 kg
Unit Type Of Package 3	P06
Number Of Units In Package 3	48
Package 3 Height	75.000 cm
Package 3 Width	60.000 cm
Package 3 Length	80.000 cm
Package 3 Weight	56.996 kg

Contractual warranty

Warranty

18 months

Sustainability Screen

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Mercury Free
Rohs Exemption Information Yes
Pvc Free

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information