

Product datasheet

Specifications



PM3210 power meter - output digital and pulse

METSEPM3210

Price: 432.60 USD

Main

Range	PowerLogic
Product Name	PowerLogic PM3000
Device Short Name	PM3210
Product Or Component Type	Power meter

Complementary

Power Quality Analysis	up to the 15th harmonic
Device Application	Power monitoring Multi-tariff Sub billing
Type Of Measurement	Active and reactive power Apparent power Current Voltage Energy Power factor Frequency Total current harmonic distortion THD (I) Total voltage harmonic distortion THD (U)
Supply Voltage	100...277 V AC 45...65 Hz 173...480 V AC 45...65 Hz 100...300 V DC
Network Frequency	50 Hz 60 Hz
[In] Rated Current	1 A 5 A
Type Of Network	3P 3P + N 1P + N
Power Consumption In Va	5 VA
Display Type	Backlit LCD
Display Resolution	128 x 96 pixels
Sampling Rate	32 samples/cycle
Measurement Current	0.05...6 A 0.02...1.2 A
Analogue Input Type	Current 0...5 A Current 0...1 A
Measurement Voltage	50...330 V AC 45...65 Hz direct 50...330 V AC 45...65 Hz phase to neutral 80...570 V AC 45...65 Hz direct 80...570 V AC 45...65 Hz phase to phase 570...999000 V AC 45...65 Hz with external VT

Excluding VAT, FCA Jabal Ali & are subject to change – check with your local distributor.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Frequency Measurement Range	45...65 Hz
Number Of Inputs	0
Measurement Accuracy	Current 0.3 % 0.5...6 A Current 0.5 % 0.1...1.2 A Voltage 0.3 % 50...330 V Voltage 0.3 % 80...570 V
Accuracy Class	Class 0.5S active energy conforming to IEC 62053-22 Class 1 active energy conforming to IEC 62053-21 Class 2 reactive energy conforming to IEC 62053-23 Class C active energy conforming to EN 50470-3
Number Of Outputs	1 pulse
Information Displayed	Tariff (4)
Communication Port Protocol	-
Communication Port Support	-
Data Recording	Time stamping 5 alarms Min/max of instantaneous values
Mounting Mode	Clip-on
Mounting Support	DIN rail
Standards	BS EN 61557-12 IEC 61557-12 EN 61557-12 BS EN 61326-1 IEC 61326-1 EN 61326-1 BS EN 62052-11 IEC 62052-11 EN 62052-11 BS EN 62053-21 IEC 62053-21 EN 62053-21 BS EN 62053-22 IEC 62053-22 EN 62052-22 BS EN 62053-23 IEC 62053-23 EN 62052-23 BS EN 61010-1 EN 61010-1 IEC 61010-1 UL 61010-1 BS EN 61010-2-30 IEC 61010-2-30 EN 61010-2-30 UL 61010-2-30 ANSI C12.20
Product Certifications	CE conforming to IEC 61010-1 (safety) CE conforming to EN 61557-12 (power monitor) CE conforming to EN/IEC 61326-1 (EMC) UKCA conforming to BS EN 61010-1 (safety) UKCA conforming to BS EN 61557-12 (power monitor) UKCA conforming to BS EN 61326-1 (EMC) CULus conforming to EN 61010-1 (safety) CULus conforming to UL 61010-1 (safety) EAC (sub-meter) RCM
Width	90 mm
Depth	70 mm
Height	95 mm
Net Weight	0.26 kg

Environment

Electromagnetic Compatibility	Electrostatic discharge level 4 conforming to IEC 61000-4-2 Susceptibility to electromagnetic fields level 3 conforming to IEC 61000-4-3 Electrical fast transient/burst immunity test level 4 conforming to IEC 61000-4-4 Surge immunity test level 4 conforming to IEC 61000-4-5 Conducted RF disturbances level 3 conforming to IEC 61000-4-6 Magnetic field at power frequency - test level: 0.5 mT conforming to IEC 61000-4-8 Conducted and radiated emissions class B conforming to EN 55022
Overvoltage Category	III
Ip Degree Of Protection	IP40 front panel: conforming to IEC 60529 IP20 body: conforming to IEC 60529
Relative Humidity	5...95 % at 50 °C
Pollution Degree	2
Ambient Air Temperature For Operation	-25...70 °C
Ambient Air Temperature For Storage	-40...85 °C
Operating Altitude	< 3000 m

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	9 cm
Package 1 Width	13.5 cm
Package 1 Length	13.5 cm
Package 1 Weight	387 g
Unit Type Of Package 2	S03
Number Of Units In Package 2	16
Package 2 Height	30 cm
Package 2 Width	30 cm
Package 2 Length	40 cm
Package 2 Weight	6.343 kg
Unit Type Of Package 3	P12
Number Of Units In Package 3	128
Package 3 Height	15 cm
Package 3 Width	80 cm
Package 3 Length	120 cm
Package 3 Weight	57.672 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓

Mercury Free

✓

Rohs Exemption Information

Yes

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information