Product datasheet

Specifications



APC Smart-UPS C 3000VA Rack mount LCD 230V

SMC3000RMI2U

Price: 1,519.00 USD

Overview	
Presentation	Intelligent and efficient network power protection from entry level to scalable runtime. Ideal UPS for servers, point-of-sale, routers, switches, hubs and other network devices.
Lead Time	Usually Ships within 2 Weeks
Main	
Main Input Voltage	230 V
Main Output Voltage	230 V
Rated Power In W	2100 W
Rated Power In Va	3000 VA
Product Or Component Type	Uninterruptible power supply (UPS)
Input Connection Type	IEC 320 C20
Output Connection Type	8 IEC 320 C13 2 IEC Jumpers 1 IEC 320 C19
Number Of Rack Unit	2U
Number Of Cables	1
Battery Type	Lead-acid battery
Provided Equipment	CD with software Documentation CD Installation guide Rack mounting brackets USB cable

Batteries & Runtime

Run Time	View Runtime Graph 🖸
Efficiency	View Efficiency Graph 🖾
Extended Runtime	0
Number Of Battery Filled Slots	0
Number Of Battery Free Slots	0
Battery Recharge Time	3 h
Number Of Battery Replacement Quantity	1
Battery Life	35 year(s)
Replacement Battery	APCRBC151
Battery Charger Power	163 W rated

Excluding VAT, FCA Jabal Ali & are subject to change - check with your local distributor.

General

Number Of Power Module Filled Slots	0
Number Of Power Module Free Slots	0
Product Web Sub-Family	Entry level
Redundant	No

Physical

Colour	Black
Height	8.9 cm
Width	48 cm
Depth	67 cm
Net Weight	41 kg
Mounting Location	Front
Mounting Preference	Lower
Mounting Mode	Rack-mounted
Two Post Mountable	0
Usb Compatible	Yes

Input

Input Voltage Limits	180287 V
Network Frequency	50/60 Hz +/- 3 Hz auto-sensing

Output

-	
Harmonic Distortion	Less than 5 %
Maximum Configurable Power In Va	3000 VA
Maximum Configurable Power In W	2100 W
Transfer Time	8 ms typical : 10 ms maximum
Ups Туре	Line interactive
Wave Type	Sine wave
Output Frequency	50 Hz sync to mains

Conformance

Product Certifications	C-Tick CE EAC GOST IRAM SABS VDE
Marking	GS Mark
Standards	EN/IEC 62040-1:2019/A11:2021 EN/IEC 62040-2:2006/AC:2006 EN/IEC 62040-2:2018

Environmental

Acoustic Level

42 dBA

Heat Dissipation	81 Btu/h
Operating Altitude	010000 ft
Ambient Air Temperature For Operation	040 °C
Ambient Air Temperature For Storage	-1545 °C
Storage Altitude	0.0015240.00 m
Relative Humidity	095 %
Storage Relative Humidity	095 %

Communications & Management

Control Panel	Multifunction LCD status and control console
Free Slots	0
Alarm	Alarm when on battery : distinctive low battery alarm : configurable delays

Surge Protection and Filtering

Surge Energy Rate	300 J
Noise Suppression	Full time multi-pole noise filtering : 0.3% IEEE surge let-through : zero clamping response time : meets UL 1449

Packing Units

-	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	25.4 cm
Package 1 Width	98 cm
Package 1 Length	60 cm
Package 1 Weight	50.9 kg

Contractual warranty

Warranty

2 years repair or replace

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Energy Efficient Take-back Transparency RoHS/REACh

Resource performance

Energy Efficient Product

Take-Back Program Available

Well-being performance

Mercury Free

Rohs Exemption Information

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information

Yes