





APC Smart-UPS,1500VA Rack Mount, LCD 230V with SmartConnect Port

SMC1500I-2UC

Price: 632.80 USD

Overview

Presentation	Intelligent and efficient network power protection from entry level to scalable runtime. Ideal UPS for servers, point-of-sale, routers, switches, hubs and other network devices.
Lead Time	Usually Ships within 2 Weeks
Main	
Main Input Voltage	230 V
Other Input Voltage	220 V 240 V
Main Output Voltage	230 V
Other Output Voltage	220 V 240 V
Rated Power In W	900 W
Rated Power In Va	1500 VA
Product Or Component Type	Uninterruptible power supply (UPS)
Input Connection Type	IEC 320 C14
Output Connection Type	4 IEC 320 C13 2 IEC Jumpers
Number Of Rack Unit	2U
Number Of Cables	1
Battery Type	Lead-acid battery
Provided Equipment	Documentation CD Installation guide Rack mounting brackets USB cable

Complementary Software Package

Software Package SmartConnect software for remote power monitoring feature availability varies by terms of use

Batteries & Runtime

Run Time	View Runtime Graph ☐
Efficiency	View Efficiency Graph ☐
Extended Runtime	0
Number Of Battery Filled Slots	0
Number Of Battery Free Slots	0

Excluding VAT, FCA Jabal Ali & are subject to change – check with your local distributor.

Battery Recharge Time	3 h
Number Of Battery Replacement Quantity	1
Battery Life	46 year(s)
Replacement Battery	APCRBC157 ☐
Battery Charger Power	112 W rated

General

Number Of Power Module Filled Slots	0
Number Of Power Module Free Slots	0
Product Web Sub-Family	Cloud-enabled monitoring
Redundant	No

Physical

Colour	Black
Height	8.6 cm
Width	43.2 cm
Depth	47.7 cm
Net Weight	28.64 kg
Mounting Location	Front
Mounting Preference	Lower
Mounting Mode	Rack-mounted
Two Post Mountable	1
Usb Compatible	Yes

Input

Input Voltage Limits	170300 V adjustable 180287 V
Network Frequency	50/60 Hz +/- 3 Hz auto-sensing

Output

Harmonic Distortion	Less than 5 %
Maximum Configurable Power In Va	1500 VA
Maximum Configurable Power In W	900 W
Transfer Time	6 ms typical : 10 ms maximum
Ups Type	Line interactive
Wave Type	Sine wave
Output Frequency	50/60 Hz +/- 3 Hz sync to mains

Conformance

C-Tick	
CE	
GOST	
VDE	
	CE GOST

Standards EN/IEC 62040-1:2019/A11:2021 EN/IEC 62040-2:2006/AC:2006 EN/IEC 62040-2:2018

Environmental

Acoustic Level	46 dBA
Heat Dissipation	90 Btu/h
Operating Altitude	010000 ft
Ambient Air Temperature For Operation	040 °C
Ambient Air Temperature For Storage	-1545 °C
Storage Altitude	0.0015240.00 m
Relative Humidity	095 %
Storage Relative Humidity	095 %

Communications & Management

Control Panel	Multifunction LCD status and control console
Free Slots	0
Communication Port Support	SmartConnect Ethernet port: for cloud monitoring feature availability varies by terms of use
Alarm	Alarm when on battery : distinctive low battery alarm : configurable delays

Surge Protection and Filtering

Surge Energy Rate	459 J
Noise Suppression	Full time multi-pole noise filtering: 0.3% IEEE surge let-through: zero clamping response time: meets UL 1449

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	25.1 cm
Package 1 Width	60.3 cm
Package 1 Length	59.4 cm
Package 1 Weight	31.91 kg

Contractual warranty

	<u> </u>
Warranty	2 years repair or replace

Sustainability Green Premium

Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >









Energy Efficient Take-back Transparency RoHS/REACh

Resource performance

Energy Efficient Product

Take-Back Program Available

Well-being performance

Mercury Free

Rohs Exemption Information

Yes

Certifications & Standards

Reach Regulation

Eu Rohs Directive

Compliant with Exemptions

Environmental Disclosure

Product Environmental Profile

Circularity Profile

End of Life Information