Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications







APC Smart-UPS SRT 3000VA RM 230V

SRT3000RMXLI

Price: 2,513.00 USD

Overview

Presentation	High density, double-conversion on-line power protection with scalable runtime.
Lead Time	Usually in Stock
Main	
Main Input Voltage	230 V
Product Or Component Type	Uninterruptible power supply (UPS)
Other Input Voltage	220 V 240 V
Main Output Voltage	230 V
Other Output Voltage	220 V 240 V
Rated Power In W	2700 W
Rated Power In Va	3000 VA
Input Connection Type	BS1363A British IEC 60320 C20 Schuko CEE 7 / EU1-16P
Output Connection Type	8 IEC 60320 C13 2 IEC Jumpers 2 IEC 60320 C19
Number Of Rack Unit	2U
Cable Length	2.44 m
Number Of Cables	1
Provided Equipment	CD with software Documentation CD Installation guide Rack mounting brackets Rack mounting support rails USB cable

Batteries & Runtime

Run Time	View Runtime Graph ☐
Efficiency	View Efficiency Graph ☐
Battery Type	Lead-acid battery
Number Of Battery Filled Slots	1
Battery Recharge Time	3 h
Number Of Battery Replacement Quantity	1

Excluding VAT, FCA Jabal Ali & are subject to change – check with your local distributor.

Warranty card

Battery Voltage	96 V
Battery Charger Power	168 W rated
Battery Life	35 year(s)
Replacement Battery	APCRBC152 ☐
Extended Runtime	1

General

Ups Type	Double conversion online
Product Web Sub-Family	High density
Number Of Power Module Free Slots	0
Number Of Power Module Filled Slots	0
Redundant	No

Physical

Colour	Black
Height	8.5 cm
Width	43.2 cm
Depth	63.5 cm
Net Weight	31.3 kg
Mounting Location	Front
Mounting Preference	Lower
Mounting Mode	Rack-mounted
Two Post Mountable	0
Usb Compatible	Yes
Mounting Position	Horizontal

Input

Network Frequency	4070 Hz auto-sensing
Input Voltage Limits	100275 V adjustable (half load)

Output

Maximum Configurable Power In Va	3000 VA
Maximum Configurable Power In W	2700 W
Output Frequency	50/60 Hz +/- 3 Hz sync to mains
Wave Type	Sine wave
Harmonic Distortion	Less than 2 %
Crest Factor	3:1
Bypass Type	Internal bypass (automatic and manual)
Additional Information	Configurable for 220 : 230 or 240 nominal output voltage

Conformance

Product Certifications	CE EAC RCM VDE
Marking	CE Mark
Standards	EN/IEC 62040-1:2019/A11:2021 EN/IEC 62040-2:2006/AC:2006 EN/IEC 62040-2:2018

Environmental

Ambient Air Temperature For Operation	040 °C
Relative Humidity	095 % non-condensing
Operating Altitude	010000 ft
Ambient Air Temperature For Storage	-1545 °C
Storage Relative Humidity	095 % non-condensing
Storage Altitude	0.0015240.00 m
Acoustic Level	55 dBA
Heat Dissipation	703 Btu/h
Ip Degree Of Protection	IP20

Communications & Management

Free Slots	1
Alarm	Audible and visible alarms : prioritized by severity
Emergency Power Off	Yes

Surge Protection and Filtering

Surge Energy Rate 340 J

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	24.6 cm
Package 1 Width	59.9 cm
Package 1 Length	87.1 cm
Package 1 Weight	39.92 kg

Contractual warranty

Warranty 3 years repair or replace (excluding battery) and 2 years for battery

Sustainability Screen Premium

Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >









Energy Efficient Take-back Transparency RoHS/REACh

Resource performance

Energy Efficient Product

Take-Back Program Available

Well-being performance

Mercury Free

Rohs Exemption Information

Yes

Certifications & Standards

Reach Regulation

Eu Rohs Directive

Compliant with Exemptions

Environmental Disclosure

Product Environmental Profile

Weee

The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Circularity Profile

End of Life Information