Product datasheet

Specifications



APC Smart-UPS SRT 3000VA 230V

SRT3000XLI

Price: 2,359.00 USD

Overview

Presentation	High density, double-conversion on-line power protection with scalable runtime.
Lead Time	Usually in Stock
Main	
Main Input Voltage	230 V
Product Or Component Type	Uninterruptible power supply (UPS)
Other Input Voltage	220 V 240 V
Main Output Voltage	230 V
Other Output Voltage	220 V 240 V

Other Output Voltage	220 V 240 V
Rated Power In W	2700 W
Rated Power In Va	3000 VA
Input Connection Type	BS1363A British IEC 60320 C20 Schuko CEE 7 / EU1-16P
Output Connection Type	8 IEC 60320 C13 2 IEC Jumpers 2 IEC 60320 C19
Cable Length	2.44 m
Number Of Cables	3
Provided Equipment	CD with software Country-specific detachable power cord Documentation CD Installation guide Removable support feet USB cable Warranty card

Batteries & Runtime

Run Time	View Runtime Graph
Efficiency	View Efficiency Graph 🗗
Battery Type	Lead-acid battery
Battery Recharge Time	3 h
Number Of Battery Replacement Quantity	1
Battery Voltage	96 V
Battery Charger Power	168 W rated

Excluding VAT, FCA Jabal Ali & are subject to change - check with your local distributor.

Battery Life	35 year(s)
Replacement Battery	APCRBC152
Extended Runtime	1

General

Ups Туре	Double conversion online
Product Web Sub-Family	High density
Number Of Power Module Free Slots	0
Number Of Power Module Filled Slots	0
Redundant	No

Physical

Colour	Black
Height	43.2 cm
Width	8.5 cm
Depth	63.5 cm
Net Weight	31.3 kg
Mounting Location	Front
Mounting Preference	Lower
Mounting Mode	Rack-mounted with kit
Two Post Mountable	0
Usb Compatible	Yes
Mounting Position	Vertical

Input

Network Frequency	4070 Hz auto-sensing
Input Voltage Limits	100275 V adjustable (half load)

Output

Maximum Configurable Power In Va	3000 VA
Maximum Configurable Power In W	2700 W
Output Frequency	50/60 Hz +/- 3 Hz sync to mains
Wave Type	Sine wave
Harmonic Distortion	Less than 2 %
Crest Factor	3:1
Bypass Type	Internal bypass (automatic and manual)
Additional Information	Configurable for 220 : 230 or 240 nominal output voltage

Conformance

Product Certifications

CE
EAC
RCM
VDE

Marking	CE Mark
Standards	EN/IEC 62040-1:2019/A11:2021 EN/IEC 62040-2:2006/AC:2006
	EN/IEC 62040-2:2018

Environmental

Ambient Air Temperature For Operation	040 °C
Relative Humidity	095 % non-condensing
Operating Altitude	010000 ft
Ambient Air Temperature For Storage	-1545 °C
Storage Relative Humidity	095 % non-condensing
Storage Altitude	0.0015240.00 m
Acoustic Level	55 dBA
Heat Dissipation	703 Btu/h
Ip Degree Of Protection	IP20

Communications & Management

Free Slots	1
Alarm	Audible and visible alarms : prioritized by severity
Emergency Power Off	Yes

Surge Protection and Filtering

Surge Energy Rate	340 J	

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	40.000 cm
Package 1 Width	80.000 cm
Package 1 Length	120.000 cm
Package 1 Weight	48.638 kg

Contractual warranty

Warranty

3 years repair or replace (excluding battery) and 2 years for battery

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Energy Efficient Take-back Transparency RoHS/REACh

Resource performance

Energy Efficient Product

Take-Back Program Available

Well-being performance

Mercury Free

Rohs Exemption Information

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information

Yes