

Product datasheet

Specifications



250V Twin Gang 13A BS Socket Module

UST426_000

⚠ Discontinued on: 30 Jun 2023

⚠ Discontinued

Main

Product Or Component Type	Socket module
Number Of Gangs	2 gangs
Rated Current	13 A at 250 V AC 50 Hz

Complementary

Load Type	Resistive
Number Of Cables	3 cable(s) 2.5 mm ² 1 cable(s) 2.5 mm ² 2 cable(s) 2.5 mm ² 1 cable(s) 4 mm ² 2 cable(s) 4 mm ²
Fixing Mode	By screws
Wiring Device Mounting	Flush Surface
Distance Between Centers	120.6 mm
Width	87 mm
Height	147 mm
Depth	16.1 mm

Environment

Ambient Air Temperature For Operation	-5...40 °C
Relative Humidity	0...95 %
Environmental Characteristic	No UV resistant
Operating Altitude	<= 2000 m
Standards	SS 145 MS 589 BS 1363-2

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.5 cm
Package 1 Width	12.2 cm
Package 1 Length	18.2 cm

Excluding VAT, FCA Jabal Ali & are subject to change – check with your local distributor.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Weight	150 g
Unit Type Of Package 2	CAR
Number Of Units In Package 2	20
Package 2 Height	18 cm
Package 2 Width	31.2 cm
Package 2 Length	56.3 cm
Package 2 Weight	4226.2 g

Contractual warranty

Warranty	18 months
----------	-----------