Product datasheet

Specifications



APC Smart-UPS SRT 5000VA RM 230V

SRT5KRMXLI

Price: 3,668.00 USD

Overview	
Presentation	High density, double-conversion on-line power protection with scalable runtime.
Lead Time	Usually in Stock
Main	
Main Input Voltage	230 V
Product Or Component Type	Uninterruptible power supply (UPS)
Other Input Voltage	220 V 240 V
Main Output Voltage	230 V
Other Output Voltage	220 V 240 V
Rated Power In W	4500 W
Rated Power In Va	5000 VA
Output Connection Type	6 IEC 60320 C13 2 IEC Jumpers 4 IEC 60320 C19
Number Of Rack Unit	3U
Provided Equipment	Documentation CD Installation guide Rack mounting hardware Rack mounting brackets Rack mounting support rails Temperature probe Warranty card Web/SNMP management card

Batteries & Runtime

Run Time	View Runtime Graph
Efficiency	View Efficiency Graph 🗇
Battery Type	Lead-acid battery
Number Of Battery Filled Slots	0
Battery Recharge Time	1.5 h
Number Of Battery Replacement Quantity	1
Battery Voltage	192 V
Battery Charger Power	560 W rated
Battery Life	35 year(s)

Excluding VAT, FCA Jabal Ali & are subject to change – check with your local distributor.

Replacement Battery	APCRBC140
Extended Runtime	1

General

Ups Туре	Double conversion online
Product Web Sub-Family	High density
Number Of Power Module Free Slots	0
Number Of Power Module Filled Slots	0
Redundant	No

Physical

Colour	Black
Height	13 cm
Width	43.2 cm
Depth	71.94 cm
Net Weight	54.43 kg
Mounting Location	Front
Mounting Preference	No preference
Mounting Mode	Rack-mounted
Two Post Mountable	0
Usb Compatible	Yes
Mounting Position	Horizontal

Input

Network Frequency	4070 Hz auto-sensing
Number Of Input Connectors	1 hard wire 3-wire (1P + N + E)
Input Voltage Limits	100275 V adjustable (half load)

Output

Maximum Configurable Power In Va	5000 VA
Maximum Configurable Power In W	4500 W
Output Frequency	50/60 Hz +/- 3 Hz sync to mains
Wave Type	Sine wave
Harmonic Distortion	Less than 2 %
Crest Factor	3:1
Bypass Type	Internal bypass (automatic and manual)

Conformance

Product Certifications

CE EAC IRAM RCM VDE

Marking	CE Mark
Standards	EN/IEC 62040-1:2019/A11:2021 EN/IEC 62040-2:2006/AC:2006 EN/IEC 62040-2:2018

Environmental

Ambient Air Temperature For Operation	040 °C
Relative Humidity	095 % non-condensing
Operating Altitude	010000 ft
Ambient Air Temperature For Storage	-1545 °C
Storage Relative Humidity	095 % non-condensing
Storage Altitude	0.0015240.00 m
Acoustic Level	55 dBA
Heat Dissipation	931 Btu/h
Ip Degree Of Protection	IP20

Communications & Management

Free Slots	1
Preinstalled Device	Network management card 3 with environmental monitoring
Alarm	Audible and visible alarms : prioritized by severity
Emergency Power Off	Yes

Surge Protection and Filtering

Surge Energy Rate

480 J

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	33 cm
Package 1 Width	61 cm
Package 1 Length	96 cm
Package 1 Weight	66.86 kg

Contractual warranty

Warranty

3 years repair or replace (excluding battery) and 2 years for battery

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Energy Efficient Take-back Transparency RoHS/REACh

Resource performance

Energy Efficient Product

Take-Back Program Available

Well-being performance

Mercury Free

Rohs Exemption Information

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information

Yes