

Product datasheet

Specifications



APC SMART-UPS SRT LI-ION 2200VA RM 230V

SRTL2200RMXLI

Price: 2,877.00 USD

Overview

Presentation	High density, double-conversion on-line power protection with scalable runtime.
Lead Time	Usually in Stock

Main

Main Input Voltage	230 V
Product Or Component Type	Uninterruptible power supply (UPS)
Other Input Voltage	220 V 240 V
Main Output Voltage	230 V
Other Output Voltage	220 V 240 V
Rated Power In W	1980 W
Rated Power In Va	2200 VA
Input Connection Type	IEC 60320 C20
Output Connection Type	6 IEC 60320 C13 2 IEC 60320 C19
Number Of Rack Unit	3U
Cable Length	1.83 m
Number Of Cables	1
Provided Equipment	CD with software Communication cable Documentation CD Installation guide Removable support feet USB cable Warranty card

Batteries & Runtime

Run Time	View Runtime Graph
Efficiency	View Efficiency Graph
Battery Type	Li-Ion (Lithium-Ion)
Number Of Battery Filled Slots	0
Number Of Battery Free Slots	0
Battery Recharge Time	4 h
Battery Voltage	48 V
Battery Charger Power	155 W rated

Excluding VAT, FCA Jabal Ali & are subject to change – check with your local distributor.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Battery Life	5...10 year(s)
Extended Runtime	1

General

Ups Type	Double conversion online
Product Web Sub-Family	Lithium-Ion
Number Of Power Module Free Slots	0
Number Of Power Module Filled Slots	0
Redundant	No

Physical

Colour	Black with silver front bezel
Height	12.8 cm
Width	43.2 cm
Depth	63.9 cm
Net Weight	30.5 kg
Mounting Preference	No preference
Mounting Mode	Rack-mounted with kit
Two Post Mountable	0
Usb Compatible	Yes
Mounting Position	Horizontal Vertical

Input

Network Frequency	40...70 Hz auto-sensing
Input Voltage Limits	160...275 V half load

Output

Maximum Configurable Power In Va	2200 VA
Maximum Configurable Power In W	1980 W
Output Frequency	50/60 Hz +/- 3 Hz sync to mains
Wave Type	Sine wave
Harmonic Distortion	Less than 2 %
Crest Factor	3 : 1
Bypass Type	Built-in bypass

Conformance

Product Certifications	CE EAC
Marking	CE Mark
Standards	EN/IEC 62040-1:2019/A11:2021 EN/IEC 62040-2:2006/AC:2006 EN/IEC 62040-2:2018

Environmental

Ambient Air Temperature For Operation	0...40 °C
Relative Humidity	0...95 % non-condensing
Operating Altitude	0...10000 ft
Ambient Air Temperature For Storage	-20...50 °C
Storage Relative Humidity	0...95 % non-condensing
Storage Altitude	0.00...15240.00 m
Acoustic Level	50 dBA
Heat Dissipation	317 Btu/h
Ip Degree Of Protection	IP20

Communications & Management

Free Slots	1
Alarm	Audible and visible alarms : prioritized by severity
Emergency Power Off	Yes

Surge Protection and Filtering

Surge Energy Rate	432 J
-------------------	-------

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	24.5 cm
Package 1 Width	87 cm
Package 1 Length	60 cm
Package 1 Weight	41.4 kg

Contractual warranty

Warranty	5 year repair or replace
----------	--------------------------

Sustainability



Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.


[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)




Energy Efficient Take-back Transparency RoHS/REACH


Resource performance

 Energy Efficient Product

 Take-Back Program Available

Well-being performance

 Mercury Free

 Rohs Exemption Information [Yes](#)

Certifications & Standards

Reach Regulation [REACH Declaration](#)

Eu Rohs Directive Compliant with Exemptions

Environmental Disclosure [Product Environmental Profile](#)

Circularity Profile [End of Life Information](#)