

# Product datasheet

Specifications



## INDICATING BANK ACCESSORIES 70MM+OPTIONS

XVC21

### Main

Range Of Product	Harmony XVB Universal
Product Or Component Type	Base unit with cover
Component Name	XVC
Material	Glass reinforced polyamide: base unit Polycarbonate: cover unit

### Complementary

Fixing Mode	Direct or tube fixing
Mounting Diameter	70 mm
Product Destination	Banks without flash discharge tube unit
Electrical Connection	1 connector for standard input
Cable Entry	Bottom or side entry
Assembly Style	Customer assembly, up to 5 units
Terminals Description Iso N°1	(GND)GROUND (COM-1)PW (COM-4)PW (COM-3)PW (COM-5)PW (COM-2)PW
Net Weight	0.19 kg

### Environment

Product Certifications	CCC EAC CSA C22-2 No 14 UL 508
Standards	IEC 60947-5-1
Protective Treatment	TC
Ambient Air Temperature For Storage	-40...70 °C
Nema Degree Of Protection	Type 4X conforming to UL (indoor)

### Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	8.500 cm
Package 1 Width	10.000 cm

Excluding VAT, FCA Jabal Ali & are subject to change – check with your local distributor.

Package 1 Length	9.500 cm
Package 1 Weight	206.000 g
Unit Type Of Package 2	S03
Number Of Units In Package 2	36
Package 2 Height	30.000 cm
Package 2 Width	30.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	8.173 kg
Unit Type Of Package 3	P06
Number Of Units In Package 3	288
Package 3 Height	75.000 cm
Package 3 Width	60.000 cm
Package 3 Length	80.000 cm
Package 3 Weight	71.516 kg

## Contractual warranty

Warranty	18 months
----------	-----------

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

## Well-being performance

Mercury Free

Rohs Exemption Information Yes

## Certifications & Standards

Reach Regulation [REACH Declaration](#)

Eu Rohs Directive Pro-active compliance (Product out of EU RoHS legal scope)

China Rohs Regulation [China RoHS declaration](#)

Environmental Disclosure [Product Environmental Profile](#)

Weee The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins


Circularity Profile No need of specific recycling operations

Dimensions Drawings

Indicator Bank without “Flash” Discharge Tube Unit

Dimensions

Below drawing shows the minimum configuration of the product. Select the number of stages according to the product characteristics in order to get **b** dimension.



- (1) Base unit
- (2) Illuminated or audible signalling unit XVBC\*\*\*, to be ordered separately
- (3) Cover (supplied with base unit)


Number of illuminated or audible signalling units (no “flash”)	b in mm	b in in.
1	138	5.43
2	201	7.91
3	264	10.39
4	327	12.87
5	390	15.35

Mounting and Clearance

Base Unit for Indicator Banks

---

Panel Cut-out for Direct Fixing



Connections and Schema

Illuminated Beacon

---

Wiring Diagram

