



Thorsman installation material, TSP-10xM5, cavity fixing, with screw, set of 25

1244003

Main

Range Of Product	Thorsman
Product Or Component Type	Cavity fixing
Device Short Name	TSP
Provided Equipment	Screw
Mounting Support	Board material - thickness: 320 mm
Device Application	320 mm board material
Mounting Support	Wall mounted
Thread Type	M5
Screw Diameter	5 mm
Screw Length	50 mm
Drilling Diameter	10 mm
Colour Tint	Blue/white

Complementary

Quantity Per Set	Set of 25
Net Weight	0.00896 kg

Environment

Material	Screw: steel electroplated Collar: PA (polyamide) Spring: PA (polyamide)
Practical Load Capacity	Shear: 250 N for 13 mm board 4.5) Pull-out load: 75 N for 13 mm board 6)
Thickness	012 mm fixture 13 mm board
Environmental Characteristic	Corrosion resistance
Ambient Air Temperature For Operation	-4080 °C
Diameter	20 mm
Length	54 mm

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1.000 cm

Package 1 Width	1.000 cm	
Package 1 Length	6.000 cm	
Package 1 Weight	9.000 q	

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

⊘	Reach Free Of Svhc	
9	Toxic Heavy Metal Free	
②	Mercury Free	
⊘	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations