

Product datasheet

Specifications



Multi-sound Siren 12/24VDC 2 Tones

XVS10BMW

Main

Range Of Product	Harmony XVS
Product Or Component Type	Siren
Device Short Name	XVS
Colour	White
Signalling Type	2 tones siren
[Us] Rated Supply Voltage	12 V AC/DC 24 V AC/DC
Noise Level	106 dB (continuous or intermittent tone) at 1 m

Complementary

Material	PC: body
Net Weight	0.8 kg
Marking	CE
[Uimp] Rated Impulse Withstand Voltage	0.8 kV
Current Consumption	300 mA at 24 V 500 mA
Clamping Connection Capacity	<= 1 x 1.5 mm²
Electrical Connection	Cable: 6.5...8.5 mm
Width	114 mm
Height	114 mm
Depth	153.2 mm

Environment

Standards	EN/IEC 60947-1 EN/IEC 60947-5-1
Protective Treatment	TC
Ambient Air Temperature For Storage	-35...70 °C
Ambient Air Temperature For Operation	-30...50 °C
Electrical Shock Protection Class	Class II conforming to EN/IEC 61140
Ip Degree Of Protection	IP53

Packing Units

Unit Type Of Package 1	PCE
------------------------	-----

Excluding VAT, FCA Jabal Ali & are subject to change – check with your local distributor.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Number Of Units In Package 1	1
Package 1 Height	19.500 cm
Package 1 Width	14.000 cm
Package 1 Length	14.000 cm
Package 1 Weight	1.032 kg
Unit Type Of Package 2	S04
Number Of Units In Package 2	8
Package 2 Height	30.000 cm
Package 2 Width	40.000 cm
Package 2 Length	60.000 cm
Package 2 Weight	9.698 kg
Unit Type Of Package 3	P06
Number Of Units In Package 3	32
Package 3 Height	75.000 cm
Package 3 Width	60.000 cm
Package 3 Length	80.000 cm
Package 3 Weight	49.792 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency

Well-being performance

✓ Mercury Free

✓ Rohs Exemption Information [Yes](#)

Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
-------------------	--

China Rohs Regulation	China RoHS declaration
-----------------------	--

Environmental Disclosure	Product Environmental Profile
--------------------------	---

Circularity Profile	End of Life Information
---------------------	---

Dimensions Drawings

Siren

Dimensions

