

Product datasheet

Specifications



impulse relay TL - 1P - 1NO - 16A - coil 12 VAC 50/60Hz- 6 VDC

15514

⚠ Discontinued on: 17 Nov 2014

⚠ End-of-service on: 1 Apr 2019

⚠ Discontinued

Main

Product Or Component Type	Impulse relay
Device Short Name	TL
Device Application	Remote control
Poles	1P
Pole Contact Composition	1 NO
[In] Rated Current	16 A
Network Type	AC
[Uc] Control Circuit Voltage	12 V AC 50/60 Hz 6 V DC

Complementary

Network Frequency	50/60 Hz
[Ue] Rated Operational Voltage	250 V AC 50/60 Hz
Control Type	Remote control Coil disconnection
Control Signal Type	Impulse
Switching Frequency	5 switching operations/minute 100 switching operations/day
Impulse Duration	50 ms...1 s
Remote Control Type	Illuminated push-button 3 mA
Local Signalling	ON/OFF indication
Mounting Mode	Fixed
Mounting Support	DIN rail
9 Mm Pitches	2
Height	84 mm
Width	18 mm
Depth	60 mm
Electrical Durability	AC-21: 200000 cycles AC-22: 100000 cycles
Range Compatibility	Multi9 ATet Multi9 ATL

Environment

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Standards	EN 669-2-2 EN 669-1
Product Certifications	GOST
Quality Labels	CEBEC IMQ VDE NF
Noise Level	60 dB
Tropicalisation	2
Relative Humidity	95 % at 55 °C
Ambient Air Temperature For Operation	-20...50 °C

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	8.5 cm
Package 1 Width	1.8 cm
Package 1 Length	7.2 cm
Package 1 Weight	0.106 kg

Contractual warranty

Warranty	18 months
----------	-----------