Product datasheet

Specifications





analog input module Modicon Quantum - 8 I multirange

140AVI03000

- ! Discontinued on: 31 Dec 2022
- ! To be end-of-service on: 31 Dec 2030

! Discontinued - Service only

Main

Range Of Product	Modicon Quantum automation platform
Product Or Component Type	Analogue input module
Type Of Filter	Single pole low pass - 3 dB at 847 Hz +/- 20 %

Complementary

Complementary	
Analogue Input Number	8
Input Type	Differential
Addressing Requirement	9 input words
Analogue Input Type	Bipolar current: 20 mA
	Bipolar voltage: +/- 10 V
	Bipolar voltage: +/- 5 V
	Unipolar current: 020 mA
	Unipolar voltage: 010 V
	Unipolar voltage: 05 V
Analogue Input Resolution	16 bits +/- 10 V
	16 bits +/- 5 V
	16 bits 010 V
	16 bits 020 mA
	16 bits 05 V
	16 bits 20 mA
Linear Measuring Range	(input range) x 1.024 mA
	(input range) x 1.024 V
Absolute Maximum Input	50 V DC
	25 mA
Input Impedance	> 20 Ohm voltage
	250 MOhm +/- 0.03 %
Absolute Accuracy Error	+/- 0.03 %
	+/- 0.05 % of full scale maximum
Linearity Error	+/- 0.008 %
Accuracy Drift According To	+/- 0.0015 % of full scale/°C
Temperature	<= 0.004 % of full scale /°C
Common Mode Rejection	> - 80 dB 60 Hz
Isolation Between Channels And	500 Vrms AC for 60 s
Bus	750 V DC
Isolation Between Channels	135 Vrms AC
	200 V DC
Update Time	10 ms
Fault Type	Broken wire 420 mA
	Overtacking scale 15 V

Marking	CE
Local Signalling	1 LED (green) for bus communication is present (Active) 1 LED (red) for external fault 8 LEDs (green) for channel is turned on 8 LEDs (red) for channel fault
Bus Current Requirement	280 mA
Power Dissipation In W	2.2 W
Module Format	Standard
Net Weight	0.3 kg

Environment

Standards	UL 508 CSA C22.2 No 142	
Product Certifications	FM Class 1 Division 2 cUL	
Resistance To Electrostatic Discharge	4 kV contact conforming to IEC 801-2 8 kV on air conforming to IEC 801-2	
Resistance To Electromagnetic Fields	10 V/m 801000 MHz conforming to IEC 801-3	
Ambient Air Temperature For Operation	060 °C	
Ambient Air Temperature For Storage	-4085 °C	
Relative Humidity	95 % without condensation	
Operating Altitude	<= 5000 m	

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5.000 cm
Package 1 Width	16.500 cm
Package 1 Length	31.500 cm
Package 1 Weight	460.000 g
Unit Type Of Package 2	\$03
Number Of Units In Package 2	7
Package 2 Height	30.000 cm
Package 2 Width	30.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	3.694 kg

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



RoHS/REACh

Well-being performance

	Reach Free Of Svhc	
⊘	Mercury Free	
⊘	Rohs Exemption Information	Yes


Certifications & Standards

Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
Circularity Profile	End of Life Information

Dimensions Drawings

Racks for Modules Mounting

Dimensions of Modules and Racks




- (1) 2 slots
- (2) 3 slots
- (3) 4 slots
- (4) 6 slots
- (5) 10 slots
- (6) 16 slots

Connections and Schema

Analog Input 8-Channel Bipolar Module

Wiring Diagram



N/C Not Connected