

Product datasheet

Specifications



Unity Hot Standby processor with multimode Ethernet - 1024 kB - 266 MHz

140CPU67160

⚠ Discontinued on: 4 July 2019

⚠ To be end-of-service on: 31 Dec 2026

⚠ Discontinued - Service only

Main

Range Of Product	Modicon Quantum automation platform
Product Or Component Type	Unity processor

Complementary

Mode Of Transmission	Multi mode
Clock Frequency	266 MHz
Number Of Slots	2 10 16 4 6
Number Of Racks	2 - local rack(s)
Number Of Distributed I/O Station	63 station(s) - 1 rack(s) - 3 Modbus Plus network(s)
Number Of Remote I/O Station	31 - 2 rack(s) per S908 remote I/O 31 - 2 rack(s) per ethernet Quantum remote I/O 16 - 2 rack(s) per ethernet X80 remote I/O
Discrete I/O Number	31744 inputs, 31744 outputs - remote 8000 inputs, 8000 outputs - distributed - per network Modbus Plus Unlimited (31 drops of 28 slots max) - ethernet remote I/O 0 - local - forbidden in Hot Standby application
Analogue I/O Number	500 inputs, 500 outputs - distributed - per network Modbus Plus Unlimited (31 drops of 28 slots max) - ethernet remote I/O 1984 inputs, 1984 outputs - remote 0 - local - forbidden in Hot Standby application
Application Specific I/O	High-speed interrupt inputs Serial link Accurate time stamping Counter
Communication Service	Ethernet router
Number Of Optional Modules	6 (Ethernet, Modbus, Modbus Plus, Profibus DP, Sy/Max)
Maximum Number Of Connections	1 USB 2 AS-Interface - distributed 4 AS-Interface - remote 6 Ethernet TCP/IP - local 6 Modbus Plus - local 6 Profibus DP - local 1 Modbus (RS232/485 Modbus/ASCII)
Integrated Connection Type	1 Modbus Plus with 1 Modbus with 1 USB with 1 optic fibre with Hot Standby

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Checks	Process control Hot standby
Memory Description	Expandable 7168 kB - program with PCMCIA card Expandable 8 MB - file storage with PCMCIA card Internal RAM 1024 kB - 512 kB for data
Switch Function	Key switch memory port on/off
Application Structure	1 periodic fast task - forbidden in Hot Standby application 128 I/O interrupt tasks - forbidden in Hot Standby application 128 interrupt tasks - forbidden in Hot Standby application 32 timer interrupt tasks - forbidden in Hot Standby application 4 auxiliary tasks - forbidden in Hot Standby application 1 cyclic/periodic master task -
Number Of Instructions Per Ms	10.28 Kinst/ms 100 % Boolean 10.07 Kinst/ms 65 % Boolean and 35 % numerical
System Overhead	0.2 ms for fast task 1 ms for master task
Bus Current Requirement	2500 mA
Local Signalling	1 LED (green) for Ethernet activity (COM) 1 LED (red) for Ethernet collision
Electrical Connection	1 female connector, connector type: SUB-D 9 for connecting to the Modbus Plus network 1 connector, connector type: RJ45 for connecting Modbus bus 1 connector, connector type: MT-RJ (multimode fiber optic) for interconnecting primary and secondary PLCs up to 4 km

Environment

Product Certifications	CE UL Misc (Marine) CSA GOST
Standards	HazLoc

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	11.0 cm
Package 1 Width	19.0 cm
Package 1 Length	32.5 cm
Package 1 Weight	1.447 kg
Unit Type Of Package 2	S04
Number Of Units In Package 2	6
Package 2 Height	30.0 cm
Package 2 Width	40.0 cm
Package 2 Length	60.0 cm
Package 2 Weight	9.629 kg


Contractual warranty

Warranty	18 months
----------	-----------

Dimensions Drawings

Racks for Modules Mounting

Dimensions of Modules and Racks



- (1) 2 slots
- (2) 3 slots
- (3) 4 slots
- (4) 6 slots
- (5) 10 slots
- (6) 16 slots