Product datasheet

Specifications





multifunction input module Modicon Quantum - 32 I - IRIG-B -DCF77

140ERT85420

() Discontinued on: 31 Dec 2022

(!) To be end-of-service on: 31 Dec 2030

Main

Range Of Product	Modicon Quantum automation platform
Product Or Component Type	Multifunction input module
Number Of Terminals	40

Complementary

Complementary	
Function Of Module	Status logging counting 500 Hz Status monitoring on discrete inputs Time and date stamped event logging
Time Synchronisation Protocol	DCF77 IRIG-B
Product Compatibility	Unity Pro V4.1 - without IRIG-B or TXSNTP100 function Unity Pro V5.0 - without IRIG-B or TXSNTP100 function Unity Pro V6.0 - without IRIG-B or TXSNTP100 function Unity Pro V7.0
Group Of Channels	2 groups of 16 inputs for process input
Discrete Input Number	1 discrete input(s) at 24 V for clock signal input 32 discrete input(s) at 24125 V for process input
Switching Voltage	125 V at 1 mA for process input 24 V at 6 mA for process input 48 V at 2.5 mA for process input 60 V at 2.5 mA for process input
Maximum Power Consumption In W	7.5 W for process input
Insulation	By optocoupler for clock signal input
Insulation Between Group Of Channels	By optocoupler
Anti Bounce Filtering	Configurable from 0 to 255 ms
Input State	Inversion configurable
Acquisition Time	1 ms for clock signal input
Input Current	5 mA for clock signal input
Electrical Connection	Cable - shielded cable <600 m for process input Cable - unshielded cable <400 m for process input
Connections - Terminals	Screw terminal block
Local Signalling	 LED (green) for communication on the bus (Active) LED (green) for self test OK, module ready (R) LED (red) for fault (F) LEDs for status of inputs (1 to 32)
Current Consumption	300 mA at 5 V DC bus 20 mA at 24125 V DC external power supply per group of channel

Module Format	Standard
Net Weight	0.45 kg

Environment

Resistance To Electrostatic Discharge	4 kV contact conforming to IEC 801-2 8 kV on air conforming to IEC 801-2
Resistance To Electromagnetic Fields	10 V/m 802000 MHz conforming to IEC 801-3
Ambient Air Temperature For Operation	060 °C
Ambient Air Temperature For Storage	-4085 °C
Relative Humidity	95 % without condensation
Operating Altitude	<= 5000 m
Protective Treatment	TC
Standards	HazLoc UL 508
Product Certifications	UL C-Tick CSA Class 1 Division 2 LR GOST Merchant Navy

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5.0 cm
Package 1 Width	16.5 cm
Package 1 Length	31.5 cm
Package 1 Weight	425.0 g
Unit Type Of Package 2	S03
Number Of Units In Package 2	7
Package 2 Height	30.0 cm
Package 2 Width	30.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	3.29 kg

Contractual warranty

Warranty

18 months

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



RoHS/REACh

Well-being performance

Reach Free Of Svhc

Mercury Free

Rohs Exemption Information Yes


Certifications & Standards

Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information

Product datasheet

Presentation

Presentation



Location of Operating Elements


- 1 Color Code
- 2 Display field (LEDs)
- 3 Terminal Block
- 4 Connection terminals
- 5 Sliding Label (inside)
- 6 Cover for the terminal blocks
- 7 Standard housing
- 8 Screws for terminal block

Product datasheet

Dimensions Drawings

Racks for Modules Mounting

Dimensions of Modules and Racks




- (1) 2 slots
- (2) 3 slots
- (3) 4 slots
- (4) 6 slots
- (5) 10 slots
- (6) 16 slots

Connections and Schema

Multifunction Input Module


Connecting the DCF77E Time Receiver



M1(1), M1(2), M1(3) : 0 VDC

- * UB(1), UB(2):24...125 VDC, UB(3): 24 VDC separate protection recommended
- ** not connected


Connecting the DCF77 of GPS Time Receiver



M1(1), M1(2), M1(3) : 0 VDC

- * UB(1), UB(2):24...125 VDC, UB(3): 24 VDC separate protection recommended
- ** not connected

Connecting the IRIG-B of GPS Time Receiver



M1(1), M1(2) : 0 VDC

* UB(1), UB(2):24...125 VDC separate protection recommended