


Product datasheet

Specifications



CDS Sc - single phase load-shedding contactor - 4 channels

15906

⚠ Discontinued on: 1 Nov 2020

⚠ Discontinued

Main

Range Of Product	Multi9
Product Name	Multi9 CDS
Product Or Component Type	Load-shedding contactor
Device Short Name	CDS Sc
Number Of Channels	4
Control And Monitoring Type	Cascade
Poles Description	1P

Complementary

Setting	60 10 30 75 45 15 90 5 25 20 50 40
Power Consumption In Va	4 VA
[Ue] Rated Operational Voltage	230 V AC +/- 10 % at 50/60 Hz
Rated Current	15 A for non-priority circuit Adjustable from 5 to 90 A for priority circuit
Local Signalling	Load-shedding indication: 4 LEDs (yellow)
Mounting Support	35 mm symmetrical DIN rail Wall mounted Panel mounting
9 Mm Pitches	16
Connections - Terminals	Non-priority circuit: screw terminal2.5...10 mm² Priority circuit: screw terminal4...50 mm²
Ip Degree Of Protection	IP40 IP20
Height	77 mm
Width	145 mm
Depth	67 mm
Net Weight	0.6 kg

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Colour	Grey (RAL 7035)
--------	-----------------

Environment

Standards	EN 50081-2 EN 50081-1 NF C 61-750
-----------	---

Ambient Air Temperature For Operation	-5...55 °C
---------------------------------------	------------

Packing Units

Unit Type Of Package 1	PCE
------------------------	-----

Number Of Units In Package 1	1
------------------------------	---

Package 1 Height	8.5 cm
------------------	--------

Package 1 Width	8 cm
-----------------	------

Package 1 Length	16 cm
------------------	-------

Package 1 Weight	0.585 kg
------------------	----------

Contractual warranty

Warranty	18 months
----------	-----------